PowerBlade



- Innovative wire & cable stripping system.
- SOG[®] knife blade with bevel edge.
- Cryogenic heat treated blade increases strength to enable longer sharpness and chip resistance.
- Manufactured from AUS 8 stainless steel.
- Lightweight tool handle military-style Zytel plastic.
- Liner Lock Blade Release System to keep knife securely locked while in-use position.

CAT. NO.	DESCRIPTION	WEIGHT
PA6575	Powerblade	.35 lbs

Keyhole/Jab Saw

Retractable Saw Set



havenue

• Integrated blade and handle design provides maximum strength.

- Ergonomic handle with non-slip grip.Hardened steel blade with clog-free teeth.
- Pointed tip easily punches through drywall for plunge cuts.
- Blade cuts on both push and pull strokes.
- Hole in handle may be used for lanyard or convenient storage.

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT
301A	23641	6" Keyhole Saw	.27 lbs

- Cuts drywall, wood, conduit, metal, pvc and plastics
- 6" blade retracts into the handle for convenience and safety.
- Accepts most 6" (or shorter) standard reciprocating saw blades and jab saw blades.
- Ergonomically designed handle allows force to be applied both on the push and pull stroke.
- · Built-in blade storage area can hold 2 additional blades.
- Adjustable blade can be used at any length or the 3 hard stops can be used for aggressive sawing.
- Jab blade and a bi-metal blade included.

Handy blade storage in tubular frame.

Complete with bi-metal blade (12"/24 TPI).

• U.S. Patent #D527,602.

faster, accurate cuts.

•

•

•

•

CAT. NO.	UPC NO.	DESCRIPTION	WEIGHT
311	13110	Retractable Saw Set	.35 lbs
311-JAB	71945	Jab Blades	_

Fully-adjustable blade tension up to 30,000 psi for longer blade life and

• Over-molded rugged design for heavy-duty use and comfort.


Alternative 45° blade mounting allows for flush cutting.

Convenient front grip feature for two-handed sawing.

Mounting for most reciprocating saw blades for extra versatility.

12" Heavy Duty Hack Saw







USA PHONE 800.435.0786 FAX 800.451.2632 CANADA PHONE 866.384.8813 FAX 800.524.2853

		REPLACEMENT PART	B ARE TOOL		GREENLEE.		
		Tubular back provid handy blade storage inside.	e	NLEE		🔎 aluminum	ty die-cast i handle is reak-proof.
					2		
Large, 4-1/2 enables dee makes handl	per cuts, 🔪			for I	etal blade design ong cutting life flexibility.	Convenier Lever mak tensioning	
enables dee	per cuts, 🔪	DESCRIPTION		for I	ong cutting life	lever mak	es blade
enables dee makes handl	per cuts,	DESCRIPTION 12" (305 mm) Heavy-Duty Hack Sa		for I and	ong cutting life flexibility.	lever mak	es blade
enables dee makes handi	per cuts, ing easy. UPC NO.		REPLA	for I and CEMENT HAC	ong cutting life flexibility. K SAW BLADES	lever mak	es blade ; a snap.
enables dee makes handl	UPC NO. 23635		REPLA CAT. N	for I and CEMENT HAC 0. UPC NO.	ong cutting life flexibility. K SAW BLADES DESCRIPTION	lever mak tensioning	es blade a snap. QTY. PER PI
enables dee makes handl CAT. NO. 333A	UPC NO. 23635		REPLA	for I and CEMENT HAC 0. UPC NO. 18 10037	ong cutting life flexibility. K SAW BLADES	lever mak tensioning Per Inch	es blade

Keyhole Saw



٠	Ergonomic-style handle with non-slip grip creates a sure	
	and comfortable feel.	

- Hardened steel blade makes cutting drywall, cement board, plastic and wood quick and easy.
- Blade goes through the handle for maximum support of the cutting blade.

CAT. NO.	UPC NO.	DESCRIPTION
301A	23641	Keyhole Saw with 6" Blade (152 mm)

PVC Saws



- "V" tooth design enables straight cuts on both push and pull saw strokes.
- Resharpenable blade.
- Pointed blade nose makes drywall surface penetration easy.
- Ergonomic handle is interchangeable with most popular PVC saw brands.

	CAT. NO.	UPC NO.	BLADE LENGTH	DESCRIPTION
	322-013	00113	13" (330 mm)	PVC Saw
R	322-113	00115	13" (330 mm)	Blade for 00113
R	322-118	00116	18" (457 mm)	Blade for 00114