

## **RocketSplice® Insulated Splicer-Reducer Connector**









## **TYPE SPAR**

## **Features**

- Transparent flexible insulating cover
- Range adjustable trim-to-fit tip
  Unique shape and compact design
- Connector, cover and cable tie packaged together
- UL Listed and CSA Certified for 600 volts
- Dual Rated

- Benefits
  No taping and allows visual inspection of splice
  Ensures proper fit of cover to cable
  Provides ease of installation, versatility and serviceability of connections made in tight spaces
  Provides ease of ordering
- Provides ease of ordering
- Ensures reliability
- Use with copper or aluminum conductor







Catalog	Wire	Dimensions			Screw
Number	Range	L	W	Н	Size & Shape
SPAR-4	4-14	3.30	1.55	.76	slotted
SPAR-2	2-14	3.83	1.75	.95	slotted
SPAR-1/0	1/0-14	4.80	1.94	1.14	3/16" socket head
SPAR-250	250kcmil-6	5.67	2.41	1.29	5/16" socket head
SPAR-350	350kcmil-10	6.17	3.29	1.79	5/16" socket head
SPAR-500	500kcmil-4	7.94	3.66	2.28	3/8" socket head

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG) Not suitable for direct burial.

DE-OX Oxide Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A/B, UL File E6207

