



Single (Thin) Wall Tubing: 3M™ FP-301 Thin-Wall Tubing

3M™ Heat Shrink Thin-Wall Tubing FP-301 Assorted Sizes Kits

The 3M™ Heat Shrink Thin-Wall Tubing FP-301 Kits are a versatile assortment of flexible polyolefin heat shrink tubing. The kits are available in two different types: Assorted Colors or Black only. Each box is constructed of rugged translucent plastic with product and installation information on the cover. Heat shrink kits allow an engineer, designer or technician to have a complete selection of popular sizes and colors for small projects and product development programs.

Material	Flexible Polyolefin
Shrink Ratio	2:1
Operating Temperature	-67 to 275°F (-55 to 135°C)
Voltage	600 Volts Max.
RoHS 2011/65/EU	Yes
Application Specifications	SAE-AMS-DTL-23053/5, Class 1, 2; AMS-3636, AMS-3637
Agency Approvals	
Manufacturing Origin	



Order No.	UPC	Description	Color	Size	Format	Case Qty.
FP301-3/32 to 1/2-Assrtd-5-133 Pc Kits	051135-37677	Each kit has 133 pieces and contains 7 colors: black, red, white, yellow, blue, green, and clear tubing in sizes of 3/32", 1/8", 3/16", 1/4", 3/8", and 1/2".	black, red, white, yellow, blue, green, and clear	3/32" (2,38 mm) 1/8" (3,18 mm) 3/16" (4,75 mm) 1/4" (6,35 mm) 3/8" (9,52 mm) 1/2" (12,7 mm)	6" (15,24 cm) pieces	133 pcs/kit, 5 kits
FP301-3/16 to 1-Black-5-102 Pc Kits	051135-38139	Each kit has 102 pieces and contains 6 sizes: 3/16", 1/4", 3/8", 1/2", 3/4", and 1".	Black	3/16" – 1" (4,75 – 25,4 mm)	6" (15,24 cm) pieces	102 pcs/pk, 5 pks