

Protect Your Outdoor Equipment

Irrigation equipment, pumps, lighting fixtures, traffic signaling devices, farm equipment, HVACR controls and motors



AG Series Surge Protective Devices



- SPD Type 1/Type 2 applications
- For outdoor installations on service entrances and utility meter cabinets
- UV resistant polycarbonate housing with ½" x 20" nominal nipple
- Type 4 outdoor rainproof enclosure
- Nominal Discharge Current 20 kA
- Green LED protection indicator
- Limited 1-year warranty



AG1BRKT Mounting Bracket

Model #	Poles	Lead Length	Wiring Config.	MCOV*		SCCR**	Voltage Protection Rating (VPR)	
				L-N/G	L-L		L-N/G	L-L
Service Voltage 120/240 VAC								
AG24013	Single Phase	18"	L1, L2, N/G	150	300	50kA	700	1200
AG2401C3	Single Phase	18"	L1, L2, N/G	150	300	50kA	700	1200
Service Voltage 208 VAC								
AG2083C3	3 Pole, 4 Wire	18"	L1, L2, L3, N/G	150	300	50kA	700	1200
Service Voltage 277/480 VAC								
AG48013	Single Phase, 2 Pole, 3 Wire	18"	L1, L2, N/G	320	640	50kA	1200	2000
AG4803C3	3 Pole, 4 Wire	18"	L1, L2, L3, N/G	320	640	50kA	1200	2000
Service Voltage 347/600 VAC								
AG6503C3	3 Pole, 4 Wire	18"	L1, L2, L3, N/G	420	840	50kA	1500	2500
AG6503L3	3 Pole, 4 Wire	36"	L1, L2, L3, N/G	420	840	50kA	1500	2500
Service Voltage 120/208/240 VAC								
AG2403C3	3 Pole, 4 Wire	18"	L1, L2, L3, N/G	150 L1/L3 - N/G 270 L2 - N/G	300 L1-L3 420 L1/L3 - L2	50kA	700 L1/L3 - N/G 1000 L2 - N/G	1200 L1-L3 1500 L1/L3-L2

*MCOV Maximum Continuous Operating Voltage

**SCCR Short Circuit Current Rating

To order AG1BRKT Mounting Bracket, see page 154