

# Primary switch mode power supplies

## CP-T, CP-S and CP-C



CP-T 24/5.0



CP-T 24/10.0  
CP-T 48/5.0



CP-A RU



CP-S 24/5.0



CP-C 24/10.0



CP-A CM

### CP-T range

Type	Three Phase Input voltage range	Rated output voltage / current	Order Code	Price
CP-T 24/5.0	340-575 V AC/ 480-820 V DC	24 V DC /5 A	1SVR427054R0000	
CP-T 24/10.0	340-575 V AC/ 480-820 V DC	24 V DC /10 A	1SVR427055R0000	
CP-T 24/20.0	340-575 V AC/ 480-820 V DC	24 V DC /20 A	1SVR427056R0000	
CP-T 24/40.0	340-575 V AC/ 480-820 V DC	24 V DC /40 A	1SVR427057R0000	
CP-T 48/5.0	340-575 V AC/480-820 V DC	48 V DC /5 A	1SVR427054R2000	
CP-T 48/10.0	340-575 V AC/ 480-820 V DC	48 V DC /10 A	1SVR427055R2000	
CP-T 48/20.0	340-575 V AC/ 480-820 V DC	48 V DC /20 A	1SVR427056R2000	

### CP-S range

Type	Input voltage range	Rated output voltage / current	Order Code	Price
CP-S 24/5.0	85-264 V AC/ 110-350 V DC	24 V DC /5 A	1SVR427014R0000	
CP-S 24/10.0	85-132 V AC, 184-264 V AC/ 220-350 V DC	24 V DC /10 A	1SVR427015R0100	
CP-S 24/20.0	85-132 V AC, 184-264 V AC/ 220-350 V DC	24 V DC / 20 A	1SVR427016R0100	

### CP-C range

Type	Input voltage range	Rated output voltage / current	Order Code	Price
CP-C 24/5.0	85-264 V AC/ 110-350 V DC	24 V DC /5 A	1SVR427024R0000	
CP-C 24/10.0	85-264 V AC/ 110-350 V DC	24 V DC /10 A	1SVR427025R0000	
CP-C 24/20.0	85-264 V AC/ 110-350 V DC	24 V DC / 20 A	1SVR427026R0000	

### Accessories

Type	Description	Order Code	Price
<b>Accessories for CP-C range</b>			
CP-C MM	Messaging module	1SVR427081R0000	
CP-C CM	Control module	1SVR427075R0000	

### Redundancy unit

Type	Suitable for decoupling CP-T, CP-S, CP-E, CP-C	Order Code	Price
CP-A-RU	2 inputs each up to 20 A and 1 output up to 40 A	1SVR427071R0000	



Full range of product and technical information place this part number in a search engine and download  
2CDC110004C0206