

# Panelboards

## Distributor Stock

*Selection*

### Pricing An Unassembled Panel

#### 400A Max. — 20" Wide x 5.75" Deep

1. Choose the appropriate Interior from the table below.
2. Choose and price the Main Device: Main Lugs from pages 11-11, Main Breaker Kit from page 11-13 and Main Breakers from Section 7.

3. Choose and price Branch Breakers. BL, BOD and NGB breakers from Section 7.
4. Choose and price Feed-Thru Lugs or Subfeed Breaker Feed-Thru Lugs from page 11-11, Subfeed Breaker Kit from page 11-11, and Subfeed Breaker from Section 7.

### Type P1 Unassembled Panelboards

Interiors Only—Less Branch Breakers			Boxes			Fronts	
Amperes Rating Mains	Max. No of Poles	Interiors	Height (inches)	Type 1	Type 3R/12 <sup>Ⓞ</sup>	Surface	Flush
<b>Convertible Mains — 1-Phase, 3-Wire</b>							
<b>120 / 240V</b>							
250	18	P1A18MC250A	32	B32	WP32	S32B	F32B
	30	P1A30MC250A	38	B38	WP38	S38B	F38B
	42	P1A42MC250A	44	B44	WP44	S44B	F44B
400	18	P1A18MC400A	56	B56	WP56	S56B	F56B
	30	P1A30MC400A	62	B62	WP62	S62B	F62B
	42	P1A42MC400A	68	B68	WP68	S68B	F68B
250	18	P1A18MC250C	32	B32	WP32	S32B	F32B
	30	P1A30MC250C	38	B38	WP38	S38B	F38B
	42	P1A42MC250C	44	B44	WP44	S44B	F44B
400	18	P1A18MC400C	56	B56	WP56	S56B	F56B
	30	P1A30MC400C	62	B62	WP62	S62B	F62B
	42	P1A42MC400C	68	B68	WP68	S68B	F68B
<b>Convertible Mains — 3-Phase, 4-Wire</b>							
<b>208Y / 120V</b>							
250	18	P1X18MC250A	32	B32	WP32	S32B	F32B
	30	P1X30MC250A	38	B38	WP38	S38B	F38B
	42	P1X42MC250A	44	B44	WP44	S44B	F44B
400	18	P1X18MC400A	56	B56	WP56	S56B	F56B
	30	P1X30MC400A	62	B62	WP62	S62B	F62B
	42	P1X42MC400A	68	B68	WP68	S68B	F68B
250	18	P1X18MC250C	32	B32	WP32	S32B	F32B
	30	P1X30MC250C	38	B38	WP38	S38B	F38B
	42	P1X42MC250C	44	B44	WP44	S44B	F44B
400	18	P1X18MC400C	56	B56	WP56	S56B	F56B
	30	P1X30MC400C	62	B62	WP62	S62B	F62B
	42	P1X42MC400C	68	B68	WP68	S68B	F68B
<b>Convertible Mains — 3-Phase, 4-Wire</b>							
<b>480Y / 277V</b>							
250	18	P1E18MC250A	32	B32	WP32	S32B	F32B
	30	P1E30MC250A	38	B38	WP38	S38B	F38B
	42	P1E42MC250A	44	B44	WP44	S44B	F44B
400	18	P1E18MC400A	46	B56	WP56	S56B	F56B
	30	P1E30MC400A	62	B62	WP62	S62B	F62B
	42	P1E42MC400A	68	B68	WP68	S68B	F68B
250	18	P1E18MC250C	32	B32	WP32	S32B	F32B
	30	P1E30MC250C	38	B38	WP38	S38B	F38B
	42	P1E42MC250C	44	B44	WP44	S44B	F44B
400	18	P1E18MC400C	56	B56	WP56	S56B	F56B
	30	P1E30MC400C	62	B62	WP62	S62B	F62B
	42	P1E42MC400C	68	B68	WP68	S68B	F68B
<b>Interiors for NGB Breakers — 3-Phase, 4-Wire</b>							
<b>480Y / 277V</b>							
250	18	P1718MC250A	32	B32	WP32	S32B	F32B
	30	P1730MC250A	38	B38	WP38	S38B	F38B
	42	P1742MC250A	44	B44	WP44	S44B	F44B
400	18	P1718MC400A	46	B56	WP56	S56B	F56B
	30	P1730MC400A	62	B62	WP62	S62B	F62B
	42	P1742MC400A	68	B68	WP68	S68B	F68B
250	18	P1718MC250C	32	B32	WP32	S32B	F32B
	30	P1730MC250C	38	B38	WP38	S38B	F38B
	42	P1742MC250C	44	B44	WP44	S44B	F44B
400	18	P1718MC400C	56	B56	WP56	S56B	F56B
	30	P1730MC400C	62	B62	WP62	S62B	F62B
	42	P1742MC400C	68	B68	WP68	S68B	F68B

<sup>Ⓞ</sup> Front included in NEMA 3R Box.

