

Stainless Steel Cable Ties and Accessories

SS - Two-Piece Solid

Strong, slip-free ties with a unique dual lock

- Low-profile, single wrap ties
- No slipping
- Dual locking mechanism



Cat. No.	For Bundle Dia. of (in./mm)	Tensile Strength (lb./N)	Width (in./mm)	Length (in./mm)	Weight (lb./kg)	Std. Pkg.
Mini Stainless Steel Cable Ties						
SS7-180	1/25	100/444.8	0.18/4.5	6.5/165	0.70/0.32	100
SS10-180	2/51			10.0/254	0.90/0.41	
SS16-180	4/102			16.0/406	1.40/0.64	
SS23-180	6/152			22.5/572	1.85/0.84	
SS29-180	8/203			29.0/737	2.35/1.07	
Standard Stainless Steel Cable Ties						
SS10-250	2/51	250/1,112	0.25/6.35	10.0/254	1.10/0.50	100
SS17-250	4/102			16.5/419	1.80/0.82	
SS23-250	6/152			22.5/572	2.50/1.13	
SS29-250	8/203			29.0/737	3.20/1.45	
SS35-250	10/254			35.0/889	3.80/1.72	

304 Stainless Steel
0.015 in. (0.38mm) Thickness
NOTE: Other lengths available on special request.
Add suffix -316 for 316 Stainless Steel.

Mini Tie Installation Tool



Perfect for mini-sized stainless steel ties

- Pocket-sized, light weight
- Applies mini-size stainless steel ties

Standard Tie Installation Tool

Pocket-sized hand tool for quick and easy cable tie installations

- Lightweight
- Applies standard-size stainless steel ties



Cat. No.	Description	Weight (lb./kg)	Std. Pkg.
WTA290	Hand tool to apply mini stainless steel cable ties; easy-to-use tool applies tension, locks tie with the dual lock, and cuts off band flush with top surface of buckle	1.17/0.53	1

Cat. No.	Description	Weight (lb./kg)	Std. Pkg.
WTA250	Hand tool to apply standard stainless steel cable ties; easy-to-use tool applies tension, locks tie with the dual lock, and cuts off band flush with top surface of buckle	1.17/0.53	1