



BURNDY Catalog Number YAL39T58
UPC Number 7818104174544
Description CANLUG-750KCML-SHORT-5/8
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	4.04
Barrell Style	Chamfered
Bolt Hole Size (in)	0.66
Barrel Type	Standard
Thickness	0.27
B Length (in)	1.41
Pad Width (in)	1.89
General	
Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 750 kcmil, 5/8" Stud, Short Barrel, Tin Plated
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	750 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	24
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175