



BURNDY Catalog Number YAL4CT14
UPC Number 78181041752
Description CANLUG-#4 STR-SHORT-1/4
Status null

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	1.53
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.73
Pad Width (in)	0.5
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	4
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175