
WALL PLATES & SPECIALTIES



SWP26LA

Screwless Polycarbonate Wall Plates

- A. Molded of rugged .065" thick polycarbonate.
- B. Seamless, sleek, super smooth construction provides no dirt-catching channel around plate's perimeter.
- C. Two-piece plastic subplate bridges recessed boxes and uneven sheet rock. Fixes floating installations.
- D. Automatic alignment pins ensure that devices are properly positioned so that wall plates fit perfectly.
- E. Oversized opening to accommodate all NEMA 26 decorator-style openings.
- F. An extra 1/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.



WALL PLATES

Specifications















Thermoset SP Series

Nylon TP Series

Screwless Polycarbonate SWP Series

302/304 Stainless Steel

Polished Brass

ed

Brushed Brass

Aluminum

Application

Legrand's broad line of Pass & Seymour® Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

Thermoset Plastic Wall Plates

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

Screwless Polycarbonate Wall Plates

- Molded of .065" thick polycarbonate, matte finish.
- 2-piece plastic subplate made of polycarbonate.
- Extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and three metallic finishes.

Metal Wall Plates


- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302/304 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.

WALL PLATES

Dimensions



Standard Size Wall Plates

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- · Available in plastic and metal only.

Dimensions

1 gang 2.75" x 4.5" 2 gang 4.56" x 4.5" 3 gang 6.375" x 4.5" 4 gang 8.125" x 4.5" 5 gang 10" x 4.5" 6 gang 11.812" x 4.5" 13.62" x 4.5" 7 gang 15.44" x 4.5" 8 gang

TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator single gang plates.

Dimensions

1 gang 2.9375" x 4.6875"
2 gang 4.75" x 4.6875"
3 gang 6.563" x 4.6875"
4 gang 8.375" x 4.6875"
5 gang 10.188" x 4.6875"
6 gang 12" x 4.6875"

Screwless Polycarbonate Wall Plates

- Available in decorator openings.
- Extra 1/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 2-piece plastic subplate made of polycarbonate.
- Available in 3 metallic finishes and 6 standard colors.

Wall Plate Dimensions

1 gang 3.10" x 4.87" 2 gang 4.912" x 4.87" 3 gang 6.724" x 4.87" 4 gang 8.536" x 4.87"

Subplate Dimensions

1 gang 2.85" x 4.62" 2 gang 4.662" x 4.62" 3 gang 6.474" x 4.62" 4 gang 8.286" x 4.62"

Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- Additional coverage for sheet rock gaps.
- Available in plastic and metal only.

Dimensions

1 gang 3.125" x 4.87" 2 gang 4.93" x 4.87" 3 gang 6.75" x 4.87" 4 gang 8.56" x 4.87"

TradeMaster® Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and decorator single gang plates.

Dimensions

1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 3 gang 6.9375" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates

- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.


Dimensions

1 gang 3.5" x 5.25" 2 gang 5.31" x 5.25" 3 gang 7.12" x 5.25" 4 gang 8.93" x 5.25"



WALL PLATES

Dimensions




Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


Wall Plate Mountings

Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.





Wall Plate Sizes

Standard Size




TradeMaster® Size Available in nylon only







TradeMaster Jumbo Available in nylon only



Jumbo




Tandem Wall Plates



Metal only. Plate mounting dimensions are non-standard. Refer to Page P-26 for details and devices that can be used.

Screwless Wall Plate Plastic Subplate



For Screwless (SWP) Wall Plate dimensions refer to Page P-4.

SPECIALTIES

Mounting Straps, Yokes & Jewels

DESCRIPTION	FINISH	COLOR	CATALOG NUMBER	DIMENSIONS						
GALVANIZED STEEL HANDY BOX PLATES										
Mounting strap for dimmer insert. Box mounted. Change from decorator to toggle opening.	Painted Steel	Ivory White Brown Light Almond	327I 327W 327 327LA	3.812"						
Mounting strap for blank insert. Box mounted. Change decorator opening to blank.	Painted Steel	Ivory White Brown Light Almond	326I 326W 326 326LA	3.812" 3.281" 3.281" 3.281" 3.281" 5.25" 5.25"						
Tandem mounting strap with two vertical openings. Plate screw hole spacing 4-3/8".	Bright Zinc		342	327 326 342						
Mounting strap with three horizontal openings. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		348	921875" 9.921875" 9.921875" 3.28125" 2.375" 3.28125" 3.28125"						
Mounting strap with single vertical opening. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		347	1.46875"						
Adjustment yoke for strap mounted telephone and blank wall plates. Slots 3-9/32" C to C. Plate screw holes 2-3/8" C to C. Box mounted.	Bright Zinc		340	348 347						
Mounting strap for blank insert. Changes toggle opening to blank, box mounted.	Thermoset	Ivory White Light Almond	80700I 80700W 80700LA	3.28125" 3.25" 3.65" 2.37" 4.07"						
				340 80700-1						

	JEWEL	CATALOG	JEWELS		JEWELS SHOWN				
	COLOR	NUMBER	FRONT VIEW	SIDE VIEW	WITH WALL PLATES				
PLASTIC JEWELS - FOR TOGGLE SWITCH OPENINGS (STYLE #1)									
Rectangular acrylic plastic warning light jewel for toggle switch plates with holding ring. Red Jewel Standard.	Red Green White	406RED 406GN 406W	T T		EMERGENCY LIGHT				
PLASTIC JEWELS - FOR SINGLE RECEPTACLE OPENINGS (STYLE #7)									
Round acrylic plastic warning light jewel for single receptacle plates with holding ring. Red Jewel Standard.	Red Green White	405RED 405GN 405W			SPECIAL OUTLET O O 259 VOLTS				

UL Listed.



DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



See specific device and wall plate catalog charts for particular color availabilities.


Metal Wall Plates

Metal Finish



Custom Metal Wall Plates Paint Finish Colors

Paint Color



To order custom metal wall plates, see Pages P-40 - P-42.

For additional colors consult factory.