Arlington

ONE-BOX™ Side Mount Vapor Boxes for Fixtures




Economical L-shaped fan/fixture boxes mount securely to joist with a shipped-in-place center screw.

FEATURES AND BENEFITS

- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Flange forms a protective barrier against air infiltration
- UL Ratings: 70 lb fan/200 lb fixture; CSA: 50 lb fan or fixture
- †2-hour fire rating

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	DESCRIPTION/ CU. IN.	UNIT PKG	STD PKG	DIM A	DIM B	DIM C	DIM D
FB442F	76220	Joist Mount Single Drywall / 15.5 Cu. In.	25	25	4.240	3.885	.562	2.948
FB443F†	76222	Fan or Fixture Single Drywall / 18.8 Cu. In.	25	25	4.240	5.183	.562	4.246
FB442FD*†	76221	Joist Mount Double Drywall / 25.0 Cu. In.	25	25	4.227	4.635	1.312	2.948
FB443FD*†	76223	Fan or Fixture Double Drywall / 28.5 Cu. In.	25	25	4.227	5.933	1.312	4.246



Add suffix "GC" to Catalog # when ordering in Canada, for example FB442FGC. Refer to chart on page R-22 for load ratings and number of single conductors.


† 2-Hour Fire Rating

PATENTED.



FBR415F

FB442FD







Non-Metallic Vapor Box with Adjustable Steel Bracket

Plastic Vapor Box with Adjustable Steel Bracket for Fans/Fixtures

FEATURES AND BENEFITS

- Fast and easy to install
- Mounts directly to a wood or steel stud for a super secure installation
- Flange forms a protective barrier against air infiltration
- UL Fan Ratings: 70 lb at 24" o.c., 110 lb at 16" o.c. UL Fixture Ratings: 90 lb at 24" o.c., 150 lb at 16" o.c. CSA Ratings: 50 lb fan/fixture at 16"-24" o.c.
- 2-hour fire rating

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	DESCRIPTION/ CU. IN.	UNIT PKG	STD PKG	DIM A	DIM B
FBR415F	72204	Joist Mount for Fan or Fixture / 18.3 Cu. In.	5	5	2.658	16" to 24"
FBR425F*	72205	Joist Mount for Fan or Fixture / 27.5 Cu. In.	5	5	3.408	16" to 24"



Add suffix "GC" to Catalog # when ordering in Canada, for example FBR415GC. Refer to chart on page R-22 for load ratings and number of single conductors. Refer to Q-16 for additional Vapor Boxes.





FBR425F

