

**CADDY PYRAMID**




CADDY PYRAMID

# CADDY PYRAMID

## CADDY PYRAMID ST Fixed Strut Support

- Provides superior support for pipe, conduit, duct, cable tray and equipment
- Foam bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Ready to use out of the box, saving installation time and labor
- Multiple sizes and load ratings offer the ability to tailor the solution to the application
- Easy to transport to the roof
- Hot-dip galvanized and UV stabilized for long lasting performance
- Supports green building requirements; thermoplastic bases are made from recycled material and can contribute to earning LEED credits



Material: Polyethylene; Polypropylene; Steel  
Finish: Hot-Dip Galvanized  
Temperature: -50 to 150 °F  
Static Load Safety Factor: 3:1

Part Number	Description	<div>F</div> <div>↓</div>
PSF6C	6" x 4.8"	300 lb
PSF10C	10" x 4.8"	1,000 lb
PSF10D	10" x 6.4"	1,000 lb
PSF16C	16" x 4.8"	1,500 lb
PSF16D	16" x 6.4"	1,500 lb

Static load at 73.1 kPa (10.6 psi) roof loading. Contact project or roofing engineer for maximum allowable load on individual project roof system.

CADDY PYRAMID

