

Decorator Devices Wide Slide TradeMaster® Series




Pass & Seymour

Features

- Convenient operation combines ON/OFF Decorator- Screw-pressure-plate back wire terminals style switch with separate slider for dimming control.
- Constant memory returns lights to previous level after a power failure.
- Sleek, ergonomic P&S Decorator-style matches other Decorator devices.
- Higher ratings.
- Single pole and 3-way operation.

- save time, space and money.
- 700W maximum rated dimmers can be ganged without de-rating.
- Package comes with three face colors -Ivory, White, Light Almond (TC).
- White only option also available (W).
- Interchangeable faces available in four colors (sold separately, see below).

Light Almond



WS700TC WSLV700TC

Shown with the Three Interchangeable Faces

All 1100W versions are 2.50" W



Preset Models

Max.	Fins Removed					
Load Rating	One Side	Two Side				
De-Ra	De-Rating Chart					
1000W	800W	700W				
1000VA	800VA	700VA				

Note: Each side removed reduces plate size by 3/8".

Catalog Number	Description	Rating	Color			
Interchangeable Face Incandescent Dimmers						
WS700TC* WS700W	Single Pole, Slide to OFF, 3 Face Colors White Face Only	120V, 700W 120V, 700W	Ivory/White/Lt. Almond White			
WS703PTC* WS703PW	Preset, Single Pole/3-Way, 3 Face Colors White Face Only	120V, 700W 120V, 700W	Ivory/White/Lt. Almond White			
WS1100TC* WS1100W	Preset, Single Pole/3-Way, 3 Face Colors White Face Only	120V, 1100W 120V, 1100W	Ivory/White/Lt. Almond White			
WS1103PTC* WS1103PW	Preset, Single Pole/3-Way, 3 Face Colors White Face Only	120V, 1100W 120V, 1100W	Ivory/White/Lt. Almond White			
Interchanged	Interchangeable Face Magnetic Low-Voltage Dimmers					
WSLV700TC* WSLV700W	Single Pole, 3 Face Colors White Face Only	120V, 700VA 120V, 700VA	Ivory/White/Lt. Almond White			
WSLV703PTC* WSLV703PW	Preset, Single Pole/3-Way, 3 Face Colors White Face Only	120V, 700VA 120V, 700VA	Ivory/White/Lt. Almond White			
Interchanged	Interchangeable Face Fan Speed Controls					
WSSC53PTC* WSSC53PW	Preset, Variable Speed, 3 Face Colors White Face Only	120V, 5A 120V, 5A	Ivory/White/Lt. Almond White			
Interchanged	Interchangeable Face Covers**					
WSKITI WSKIT WSKITBK	Wide Slide Interchangeable Face, White		Ivory Brown Black			
WSKITLA	,		Light Almond			
WSKITPI WSKITP WSKITPBK	VSKITP Present Wide Slide Interchangeable Face, Brown		Ivory Brown Black			
1	1 Tooth Wide Olide Interesting Capital Co., Didok					

^{*}Available in VisionPak™ packaging, add "CCV6" to Catalog Number. Example: WS700TCCCV6.

No-Noise De-Hummers


WSKITPLA

Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3 or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

Present Wide Slide Interchangeable Face, Light Almond

Catalog Number	Description	Ratings	Color		
	o-Noise De-Hummer Specification Grade Controls – RFI Protected				
94084I* 94084W* 94084GRY 94084LA*	3-Speed, Single Pole	120V 1.5A max.	Ivory White Gray Light Almond		

^{*} Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94084LAV.





94084

^{**}Available in VisionPak™ packaging, add "BPCC6" to Catalog Number. Example: WSKITIBPCC6.

Devices & Wall Plates Color Selection Chart









To order custom metal wall plates, see Pages Q-43 - Q-45.

For additional colors consult factory.