PLUGMOLD[®] NM2000 SERIES[™]



Two-piece, single channel raceway. Easy-to-install and ideal for basic power or communication installations.

CODE REFERENCE

cULus Listed Base & Blank Cover: File E4376 Guide RJBT.

Multioutlet Assemblies: File E15191 Guide PVGT.

Fittings: File E41751 Guide RJPR.


Base and Blank Cover and Plugmold Series with Snapicoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC.

Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.

KEY Plugmold NM2000 Series System Layout A. NM2010A Entrance End Fitting Plugmold NM2010A B. NM2010B Blank End Fitting C. NM2051H Horizontal Wall Box Adapter D. NM2006 Cover Clip Plugmold E. NM2017 Internal Elbow Е F. NM2015 Tee Fitting Plugmold G. NM2048-2 Two-Gang Device Box H. NM2018 External Elbow I. NM2048 Single-Gang Device Box G J. NM2011 Flat Elbow K. NM2010A Entrance End Fitting NM2051V Vertical Wall Box L. Adapter Plugmold Plus Multioutlet System NOTE: Illustration is for showing product applications only.

COLOR OPTIONS


Plugmold[®] Plus NM2000 Series[™] Part Numbers without a prefix have an ivory finish unless otherwise specified. Custom color options are also available. Consult the factory for more information.



PLUGMOLD[®] NM2000 SERIES[™] Ordering Information

Plugmold NM2000 Series Ordering Information (continued)

NM2000BC Base and Cover




NM2000B and NM2000C packed ten 5' [1.5m] lengths of each per carton.

NM2000B Raceway Base

Single channel plastic base, ivory finish. Packed ten 8' [2.4m] lengths per carton.

NM2003 Supporting Clip



Supports lengths of raceway at any point desired. Mount to surface with No. 8 flathead screw.

NM2006 Cover Clip

[38mm]






Covers seam where lengths of cover or base meet.

NM2000C Raceway Cover

1 3/4" [44mm]

Tapered snap-on cover. Textured ivory finish. Packed ten 8' [2.4m] lengths per carton.

W30/W30G Pressure-Type Wire Connectors




W30 - For common connection of two, three, or four No. 12 or No.14 solid copper conductors.

W30G – For connection of equipment grounding of 2, 3, or 4 solid conductors No. 14 or No. 12 AWG. 300V maximum; 20A 105° C maximum.


NOTE: Not for use with aluminum conductors.

NM2000WC Wire Clip




Holds wire or cable in place or for use when conductors bypass receptacles.

NM2010A Entrance End Fitting



To end feed raceway or Plugmold strip. Has 1/2" trade size KO on end and bottom.

NM2010B Blank End Fitting



Closes off open end of NM2000 Series Raceway.

NM2011 Flat Elbow

