



**BURNDY Catalog Number** YAV8T38B  
**UPC Number** 7818104291299  
**Description** CANLUG- 8 FLEX-3/8-BELL  
**Status** Active

**Web Use**  
 BURNDY Product Line

**Dimensional**  
 Tongue Angle Straight  
 Length (in) 1.32  
 Barrell Style Belled  
 Bolt Hole Size (in) 0.39  
 Barrel Type Standard  
 Thickness 0.06  
 B Length (in) 0.45  
 Pad Width (in) 0.57

**General**  
 Number of Holes 1  
 Product Description Pure Electrolytic Seamless Cu  
 Tube Compression Terminal, 1  
 Hole W/InspWindow, #8 AWG  
 Flex, 3/8" Stud, Belled End

**Conductor(s)**  
 Aircraft Cable Size (Range) N/A  
 Flex (Class H) Size - Range 8 AWG  
 Flex (Class I) Size - Range 8 AWG  
 Copper Solid Size (Range) N/A  
 DLO Size (Range) N/A  
 Navy Cable Size (Range) N/A  
 Copper Stranded (Range) N/A  
 Flex (Class G) Size - Range 8 AWG  
 Flex (Class M) Size - Range 8 AWG

**Physical**  
 Type of Plating Tin - Electro Plated  
 Bolt Hole Size 3/8  
 Plated (Yes or No) Y  
 Product Material Copper

**Approvals / Certifications**  
 UL Listed N  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N

**Documentation**

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive  
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175