







# **CIRCUIT VERIFYING**

## **Polarity Cubes**



#### GT-10

- · Use to troubleshoot 120 V AC grounded outlets.
- · Light sequence indicates correct/incorrect wiring.
- · Lifetime Limited Warranty

#### GT-10GFI

- Use to troubleshoot 120 V AC grounded outlets and test GFCI receptacles.
- · Light sequence indicates correct/incorrect wiring.
- · Lifetime Limited Warranty

CAT. NO.	UPC NO.	DESCRIPTION
GT-10	12124	Cube, Polarity
GT-10GFI	12125	Tester, Circuit GFI

### **GFCI and Circuit Tester**



- Allows instant testing of GFCI receptacles or GFCI circuit breaker protected circuits.
- Checks 120VAC grounded outlets for correct/incorrect wiring.
- LED indicators signal correct wiring, open ground, open neutral, open hot, hot/ground reversed and hot/neutral reversed.
- · Lifetime Limited Warranty

#### **SPECIFICATIONS**

Capacity 120VAC, 3-wire systems
Time 4-second interval between mA test impulses;

200 ms pulse duration

**Size** 5-3/8" x 2-5/8" x 1-3/4" (137 mm x 67 mm x 44 mm)

**Cord length** 16" (406 mm) **Weight** 0.5 lb. (227g)

Accuracy Current: 10% at nominal voltage; Time: approx. 12%

Measurement Category CAT II, 150V

CAT. NO.	UPC NO.	DESCRIPTION
5708	34523	GFCI and Circuit Tester
5708-C*	07640*	GFCI and Circuit Tester

\* Includes Certificate of Calibration