

# UNDER CABINET RANGE HOODS

## RLC SERIES

This hood is for ducted operation only. 160 cfm, 6.5 sones (vertical or horizontal discharge). HVI certified.



Part No.	Description	Width	CFM	Sones	Weight (lb.)	UPC
RL6130WWC	White on white - ducted only	30"	160	6.5	14	784891988301

## PM SERIES

The Power Module series range hood features a fully enclosed design and multi-speed operation in your choice of two performance levels - 250 cfm, 390 cfm.



Part No.	Description	Width	CFM	Sones	Weight (lb.)	UPC
PM250	Silver	20 1/2"	250	8.0	8.4	026715172955
PM390	Silver	20 1/2"	390	6.0	16	026715172962

## ACCESSORIES

Part No.	Description	Size	Weight (lb.)	UPC
35	Wall hanging kit for mounting hoods to wall when cabinets are not used	-	2	026715021697
BP87	7" round damper (for 7" round duct installation) - PM250 only	-	0.5	40026715049897
LLMM7C	7" round transition (for 7" round duct installation)	-	1	784891310720
LT30	Liner 30", T-shape for PM250 and PM390 (cabinet 12" deep)	30" x 16 1/2" x 4"	7	026715172979
LT36	Liner 36", T-shape for PM250 and PM390 (cabinet 12" deep)	36" x 16 1/2" x 4"	8	026715172986
LB30	Liner 30", box shape for PM250 and PM390 (cabinet 18" deep)	28 7/16" x 17 1/4" x 4"	7	026715172993
LB36	Liner 36", box shape for PM250 and PM390 (cabinet 18" deep)	28 7/16" x 17 1/4" x 4"	8	026715173006
356NDK	Non-ducted kit for PM250	26 3/8" x 10 13/16" x 10 13/16"	-	026715174232
357NDK	Non-ducted kit for PM390	20 3/8" x 14 3/8" x 13 1/4"	-	026715174249