STRAIGHT BLADE RECEPTACLES

STRAIGHT BLADE RECEPTACLES





Twist, click, screw, DONE.

Your productivity gains being at rough-in.

Instead of making pigtails, simply connect the pre-stripped PlugTail™ Connector leads. In one simple step, you're ready for fast, easy device installation at any time.

Device installation takes less than a minute.

Just plug the connector into the PlugTail device.

- no preparing, stripping or looping the conductors
- no taping terminals
- no mistakes resulting in rework or callbacks

A faster, more reliable installation.

PlugTail installation is three times faster than conventional device installation – saving you the most time at the end of the project when you're fighting completion pressure. With no exposed terminals, you can power-up and test a circuit at any time once the connectors are installed.

Whether the work is done by a first-year apprentice or by your most experienced installer, every PlugTail device will be installed correctly.

Happier installers. Happier customers.

Because PlugTail installation's a lot easier on the knees and fingers, your installers benefit. And because it delivers dependability, quality and easier, safer service for years to come, your customers benefit, too.









Featured Products







STRAIGHT BLADE RECEPTACLES

PlugTail™ Extra Heavy-Duty Specification Grade Receptacles




PT5362AW Duplex Receptacles

- A. Auto-ground clip ensures positive ground.
- **B. Exclusive patented feature, circuit label on face** allows permanent circuit identification.
- C. .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- D. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- **E. No exposed terminals** create a finger-safe application before, during, and after installation.
- **F. Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
- **G. Large crimped and welded brass contacts** snugly terminate on device blade terminals.
- H. Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.
- Exclusive patented feature, circuit label on back allows permanent circuit identification.
- J. Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Two drive screws anchor strap to back body and face.


Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.





STRAIGHT BLADE RECEPTACLES

Specification Grade Single Receptacles 15 & 20A, 125 & 250V



Features

- Auto-ground clip assures positive
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zincplated steel strap for added strength.
- One-piece brass triple-wipe power contacts for lasting retention.

					3rd PARTY	COMPLIANCE
	RATING			NEMA	(h)	@ -
CATALOG NUMBER	Α.	٧.	COLOR	CONFIG. NO.	UL498	C22.2 No. 42
SINGLE RECEPTACLES	SIDE WI	RE				
52511	15	125	lvory	5-15R	•	•
5251W	15	125	White	5-15R	•	•
5251	15	125	Brown	5-15R	•	•
5251LA	15	125	Light Almond	5-15R	•	•
53511	20	125	lvory	5-20R	•	•
5351W	20	125	White	5-20R	•	•
5351	20	125	Brown	5-20R	•	•
5351LA	20	125	Light Almond	5-20R	•	•
56511	15	250	Ivory	6-15R	•	•
5651W	15	250	White	6-15R	•	•
5651	15	250	Brown	6-15R	•	•
5651LA	15	250	Light Almond	6-15R	•	•
58511	20	250	lvory	6-20R	•	•
5851W	20	250	White	6-20R	•	•
5851	20	250	Brown	6-20R	•	•
5851LA	20	250	Light Almond	6-20R	•	•
SHORT STRAP SINGLE	RECEPT	ACLES SCRE	W SPACING 2.370"			
5251SSIB	15	125	lvory	5-15R	•	•
5251SSWB	15	125	White	5-15R	•	•
5251SSBKB	15	125	Black	5-15R	•	•
5251SSLAB	15	125	Light Almond	5-15R	•	•
SINGLE RECEPTACLES	SIDE WI		GLE SLOTS		_	
53711	20	125	lvory	Non-NEMA	•	•
5371W	20	125	White	Non-NEMA	•	•
5371	20	125	Brown	Non-NEMA	•	•
SHORT STRAP SINGLE						
52581	15	125	lvory	5-15R	•	•
5258W	15	125	White	5-15R	•	•
5258	15	125	Brown	5-15R	•	•
5258BK	15	125	Black	5-15R	•	•
53581	20	125	lvory	5-20R	•	•
5358W	20	125	White	5-20R	•	•
5358	20	125	Brown	5-20R	•	•
5358BK	20	125	Black	5-20R	•	•
56581	15	250	lvory	6-15R	•	•
5658	15	250	Brown	6-15R	•	•
5858I	20	250	lvory	6-20R	•	•
5858W	20 20	250 250	White	6-20R 6-20R	•	•
5858	20	250	Brown	o-ZUK	•	•

2 Pole, 3 Wire





NEMA 5-15R

5-20R

 \bigcap G _ _

NEMA 6-15R

NEMA 6-20R

For Bulk Packaging Solutions consult factory.

Supplied with mounting screws.