B. Copper Systems

C. Fiber **Optic** Systems

Power over **Ethernet** 

E. Zone Cabling

F. Wireless

G. Outlets

Media Distribution

Ι. **Physical** Infrastructure Managemen

J. Overhead 8 Underfloor Routing

Surface Raceway

Cabinets, Racks & Cable Management

M. Grounding & **Bonding** 

Industrial

0. Labeling & Identificatio

Cable Manageme Accessories

> Q. Index


## **N**° ( E Panduct® Type G – Wide Slot Wiring Duct


## Specifications

- Material: Lead-free PVC
- UL Recognized continuous use temperature: 122°F (50°C)
- UL94 flammability rating of V-0
- Conforms with NFPA 79-2007 section 13.3.1 requirement for flame retardant material
- · Provided with mounting holes
- · Base and cover length is 6 feet

## **Features and Benefits**

- · Wide finger design provides greater rigidity and larger slot width
- · Panduit exclusive rounded edges will not cut hands or abrade wiring insulation
- · Non-slip cover will not slide easily when installed on duct base
- Flush cover design holds more wires than traditional duct designs
- Double scoreline saves installation time and lowers installed cost
- Specially formulated lead-free material eliminates health concerns associated with PVC that contains lead
- · Restricted slot design retains wire in slot for fast, easy wire installation or removal







To order cover with protective film add "-F" to part number.

Page	Duct Size (W x H)		Cover Post	Std. Pkg.	Base Ctn.	Cover Ctn.
Base Part Number	In.	mm	Cover Part Number	Qty. (Ft.)	Qty. (Ft.)	Qty. (Ft.)
G.75X2BL6	0.93 x 2.03	23.6 x 51.7	C.75BL6	6	120	120
G1X1BL6	1.26 x 1.12	32.0 x 28.4	C1BL6	6	120	120
G1X1.5BL6	1.26 x 1.62	32.0 x 41.1	C1BL6	6	120	120
G1X2BL6	1.26 x 2.12	32.0 x 53.8	C1BL6	6	120	120
G1X3BL6	1.26 x 3.12	32.0 x 79.2	C1BL6	6	120	120
G1X4BL6	1.26 x 4.10	32.0 x 104.1	C1BL6	6	60	120
G1.5X1.5BL6	1.75 x 1.62	44.5 x 41.1	C1.5BL6	6	120	120
G1.5X2BL6	1.75 x 2.12	44.5 x 53.8	C1.5BL6	6	120	120
G1.5X3BL6	1.75 x 3.12	44.5 x 79.2	C1.5BL6	6	120	120
G1.5X4BL6	1.75 x 4.10	44.5 x 104.1	C1.5BL6	6	60	120
G2X1BL6	2.25 x 1.12	57.2 x 28.4	C2BL6	6	120	120
G2X2BL6	2.25 x 2.12	57.2 x 53.8	C2BL6	6	120	120
G2X3BL6	2.25 x 3.12	57.2 x 79.2	C2BL6	6	60	120
G2X4BL6	2.25 x 4.10	57.2 x 104.1	C2BL6	6	60	120
G2.5X3BL6	2.75 x 3.12	69.9 x 79.2	C2.5BL6	6	120	120
G3X2BL6	3.25 x 2.12	82.6 x 53.8	C3BL6	6	120	120
G3X3BL6	3.25 x 3.12	82.6 x 79.2	C3BL6	6	60	120
G3X4BL6	3.25 x 4.10	82.6 x 104.1	C3BL6	6	60	120
G4X2BL6	4.25 x 2.12	108.0 x 53.8	C4BL6	6	60	120
G4X3BL6	4.25 x 3.12	108.0 x 79.2	C4BL6	6	60	120
G4X4BL6	4.25 x 4.10	108.0 x 104.1	C4BL6	6	60	120
G4X5BL6	4.25 x 5.10	108.0 x 129.5	C4BL6	6	60	120

For other colors replace BL (Black) with LG (Light Gray) or WH (White). Order number of feet required, in multiples of 6' or Standard Carton Quantity. Height dimension includes duct with cover. Base and cover sold separately.





	E	F
For 0.5" Duct Height:	0.31" (9.4)	0.80" (20.3)
0.75" to 2" Duct Height:	0.31" (7.9)	0.80" (20.3)
3" to 4" Duct Height:	0.31" (7.9)	1.00" (25.4)
5" Duct Height:	0.38" (9.4)	1.33" (33.8)