Straight Blade Devices Insulgrip[®] and Valise[®] 15 and 20 Ampere Plugs and Connectors Features and Benefits

W

Individually molded face for each blade configuration keeps debris out of plug interior

Roomy wiring chamber provides — ample space for wiring

Individual wiring terminals completely enclosed in their own separate chambers

Powerful, offsetting cord grips clamp on individual conductors and outer cord jacket to prevent strain on terminals

Ribbed nylon housing is impact – and chemical resistant

Beveled housing prevents snagging — when dragged across uneven surfaces



Integral VARI-SIZE® insert adjusts to a wide range of cord sizes: .23 to .72 inch (5.8 to 18.3).



VARI-SIZE® pointer set to "smaller than gauge" position. Cord diameter range is .23 to .36 inch (5.8 to 9.0). Accepts slotted and Phillips head drivers.





grip screws deter slippage of the screwdriver.. Powerful offsetting cord grips clamp on

Multiple drive screws

provide screwdriver

versatility. Pocketed

recess for cord

HBL5266C

cord grips clamp on individual conductors and outer cord jacket to prevent strain on terminations.






Catalog number is visible on the device while in use for easy identification.

Transparent angled wiring entrance holes permit "straight in" conductor insertion

Valise[®] Plug





4.62" (117.3)

မြာ Acceptor [®] Hazardous Location Receptacles	15A 125V NEMA 5-15R UL CSA 0.5 HP	20A 125V NEMA 5-20R UL CSA 1 HP	3.00"
Description	Catalog Number		R AND
Explosion and dust ignition proof. Class I, Div. 1 & 2, Groups C, D Class II, Div. 1 & 2, Groups F, G Class III NEMA® 3, 7 B C D, 9 F G		UGRO20231 UGRA20231*	UGR020231

Note: *UGRA version includes an adapter plate for mounting to Crouse-Hinds[®] EDS series and Appleton[®] EFD series back boxes. UL Listed for Class 1, Div. 2, Groups B, C, D.

لی کی Acceptor® Hazardous Location Plugs	15A 125V NEMA 5-15P UL CSA	20A 125V NEMA 5-20P UL CSA	2.55° (64.8) 1.51° (38.4) UGP15231
Description	Catalog Number		0GF 15251
Explosion and dust ignition proof. Class I, Div. 1 & 2, Groups B, C, D Class II, Div. 1 & 2, Groups E, F, G Class III NEMA [®] 3, 7 B C D, 9 F G	UGP15231	UGP20231	200#ogs#



SWB Series Boxes

Hub Size	1-Gang Dead End	1-Gang Feed Thru
1/2 in. NPT	SWB1	SWB4
¾ in. NPT	SWB2	SWB5
Class I, Div. 1 & 2, Groups C, D		
Class II, Div. 1 & 2, Groups E, F, G		
Class III		
NEMA® 7 C D, 9 E F G		

Note: SWB series boxes will only accommodate Acceptor Series receptacles, not standard weatherproof covers.



NEMA® is a registered trademark of the National Electrical Manufacturers Association.