

## Scotch® Self-Fusing Silicone Rubber Electrical Tape 70HDT

Scotch® Self-Fusing Silicone Rubber Electrical Tape 70HDT is the heavy duty version of Scotch® Self-Fusing Silicone Rubber Electrical Tape 70, a high-temperature, arc- and track-resistant tape composed of self-fusing, inorganic silicone rubber with an easy-tear and easy-strip liner. Scotch® Rubber Tape 70HDT also has a triangular tapered edge profile (thicker in the middle) and a blue guideline to make half-lapping application easier.

<b>Material</b>	Inorganic Silicone Rubber
<b>Tape Grade</b>	Premium
<b>Tape Type</b>	Insulating and Splicing
<b>Operating Temperature</b>	Up to 356°F (180°C)
<b>RoHS 2011/65/EU</b>	Yes
<b>Specifications</b>	AA-59163 Class-I Type I; ASTM D-1000-76; ASTM D-495-71
<b>Country of Origin</b>	Canada



Order No.	UPC	Color	Length	Width	Thickness	Elongation	Breaking Strength	Rolls per Carton	Rolls per Case
70HDT-1x30FT	051128-57262	Sky Blue Gray with Guideline	30'	1.00"	Center: 20 mil Edges: 8 mil	300%	14 lbs/in	1	24

## Scotch® Fire-Retardant and Electric Arc Proofing Tape 77 Series

Scotch® Fire and Electric Arc Proofing Tape 77/77W is designed to protect most types of electrical cables when exposed to potential failures in an adjacent cable. Its specially formulated adhesive expands in fire to form a thick char buildup between the flame and the cable. The resulting firewall acts as a heat shield and flame barrier, thus protecting the nearby cables and accessories.

<b>Adhesive Material</b>	Non-adhesive
<b>Backing Material</b>	Intumescent Elastomer
<b>Tape Grade</b>	Premium
<b>Tape Type</b>	Insulating and Splicing
<b>RoHS 2011/65/EU</b>	Yes
<b>Specifications</b>	ASTM D-2863; ASTM C-518; Consolidated Edison Co. Test EO-5343-14
<b>Country of Origin</b>	



Order No.	UPC	Color	Length	Width	Thickness	Breaking Strength	Rolls per Carton	Rolls per Case
77 White-1-1/2x20ft	051128-60334	White-Gray	20'	1.50"	30 mil	36 lbs/in	1	10
77 White-3x20ft	051128-60335	White-Gray	20'	3.00"	30 mil	36 lbs/in	1	10
77 Black-1.5"x20'	051128-60332	Black	20'	1.50"	30 mil	36 lbs/in	1	10
77 Black-3"x20'	051128-60333	Black	20'	3.00"	30 mil	36 lbs/in	1	10