

# AG3000

## HVAC Surge Protective Device



### AG3000 HVAC Surge Protective Device



- Meets ANSI UL1449 3rd Edition Standards
- 120/240 VAC single split phase SPD for use on a variety of HVAC equipment
- Green LED protection indicator
- Type 4x enclosure
- ½" x 20 threaded nipple (weatherproof and UV resistant)
- TPMOV™ technology
- 3 modes of protection
- 3 leads
- 18" lead length
- 10 gauge leads
- 3-year warranty
- \$7,500 connected equipment warranty

Model #	Service Voltage	SPD Type	Nominal Discharge Current	MCOV*		Wiring Configuration	SCCR**	Voltage Protection Rating (VPR)		
				L-N	L-L			L-N/G	N-G	L-L
AG3000	120/240 VAC	1 or 2	10kA	150V	300V	L1, L2, L/N-G	20kA	600		900

\* MCOV Maximum Continuous Operation Voltage

\*\*SCCR Short Circuit Current Rating