

Sentron Molded Case Circuit Breakers

SND 1200A Frame, Digital Solid State Sentron Sensitrip III Series[®]

Selection

Type SND6

Blue Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SND69800A■	800	
SND69100A■	1000	
SND69120A■	1200	
SND69800AG■	800	
SND69100AG■	1000	
SND69120AG■	1200	
SND69800ANT■	800	
SND69100ANT■	1000	
SND69120ANT■	1200	
SND69800ANGT■	800	
SND69100ANGT■	1000	
SND69120ANGT■	1200	

Type SHND6

Black Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SHND69800A■	800	
SHND69100A■	1000	
SHND69120A■	1200	
SHND69800AG■	800	
SHND69100AG■	1000	
SHND69120AG■	1200	
SHND69800ANT■	800	
SHND69100ANT■	1000	
SHND69120ANT■	1200	
SHND69800ANGT■	800	
SHND69100ANGT■	1000	
SHND69120ANGT■	1200	

Current Limiting

Type SCND6

Red Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SCND69800A■	800	
SCND69100A■	1000	
SCND69120A■	1200	
SCND69800AG■	800	
SCND69100AG■	1000	
SCND69120AG■	1200	
SCND69800ANT■	800	
SCND69100ANT■	1000	
SCND69120ANT■	1200	
SCND69800ANGT■	800	
SCND69100ANGT■	1000	
SCND69120ANGT■	1200	



SND 1200A Frame – 100% Rated[Ⓛ]

Type SND6-H

Blue Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SND69800AH■	800	
SND69100AH■	1000	
SND69120AH■	1200	
SND69800AGH■	800	
SND69100AGH■	1000	
SND69120AGH■	1200	
SND69800ANTH■	800	
SND69100ANTH■	1000	
SND69120ANTH■	1200	
SND69800ANGTH■	800	
SND69100ANGTH■	1000	
SND69120ANGTH■	1200	

Type SHND6H

Black Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SHND69800AH■	800	
SHND69100AH■	1000	
SHND69120AH■	1200	
SHND69800AGH■	800	
SHND69100AGH■	1000	
SHND69120AGH■	1200	
SHND69800ANTH■	800	
SHND69100ANTH■	1000	
SHND69120ANTH■	1200	
SHND69800ANGTH■	800	
SHND69100ANGTH■	1000	
SHND69120ANGTH■	1200	

Current Limiting

Type SCND6-H

Red Label

3-Pole, 600V AC		
Catalog Number	Max Current Rating	List Price \$
SCND69800AH■	800	
SCND69100AH■	1000	
SCND69120AH■	1200	
SCND69800AGH■	800	
SCND69100AGH■	1000	
SCND69120AGH■	1200	
SCND69800ANTH■	800	
SCND69100ANTH■	1000	
SCND69120ANTH■	1200	
SCND69800ANGTH■	800	
SCND69100ANGTH■	1000	
SCND69120ANGTH■	1200	

Trip Unit Adjustable Functions

Suffix Letter Code	Trip Type	Cont Current Setting	Long Time Delay	Instantaneous Setting	Short Time Pick Up	Short Time Delay	Short Time I ² t Pick Up	Ground Fault Pick Up	Ground Fault Delay
A	LI	✓	✓	✓					
AG	LIG	✓	✓	✓				✓	✓
ANT	LSI	✓	✓	✓	✓	✓	✓		
ANGT	LSIG	✓	✓	✓	✓	✓	✓	✓	✓

Interrupting Ratings

Breaker Type	RMS Symmetrical kA UL 489 (File E10848)		
	240V AC	480V AC	600V AC
SND6	65	50	25
SHND6	100	65	50
SCND6	200	100	65

Neutral Transformers

Ampere Rating	Catalog Number	List Price \$
800	N08SMDA	
1000	N10SNDA	
1200	N12SNDA	

For inches / millimeters conversion, see Application Data section.

For ordering information and terminal connectors, and enclosures, see page 17/81.

Note: "G" suffix in catalog number denotes circuit breaker for 3-phase, 3-wire circuits.

For 3-phase, 4-wire, order correct 4th wire (neutral) transformer as separate and additional item.

■ Built to order. Allow 2-3 weeks for delivery.

Ⓛ Use 2-3TA4P8500 for 3-pole. These kits are rated for 90°C wire. 90°C Cu only cable must be used, and sized per 75°C ampacity.

Ⓜ SND6, SHND6 and SCND6 circuit breakers are UL Listed for reverse connection applications.