

Photo Not Available



BURNDY Catalog Number CJC29C26  
UPC Number 7818104191688  
Description 3/0-250 TO 6-2/0 CU GRD  
Status Active

Web Use  
BURNDY Product Line

	Dimensional
Length (in)	0.75
Height (in)	1.97
	General
Product Description	Cu Compression Ground Tap Connector, 3/0 Str. - 250 Kcmil (Run), 6 Sol. - 2 Str. (Tap)
	Conductor(s)
Copper Tap Range	6 AWG-2 AWG
Copper Stranded Run (Range)	3/0 AWG-250 kcmil
Rod Size Run (Range)	N/A
Copper Solid Tap (Range)	6 AWG-2 AWG
Rebar Run Size (Range)	N/A
Copper Solid Run Size (Range)	3/0 AWG-4/0 AWG
	Physical
Type of Plating	Unplated
Connector Type	Tap
Plated (Yes or No)	N
Index Number	CSA28CU
Product Material	Copper
	Approvals / Certifications
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive  
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175