

DEVINE Dimmers and Fan Controls

Single-Pole & 3-Way
600W/VA, 1000W/VA, 8A, 1.5A
Incandescent, Halogen, Magnetic Low-Voltage,
Electronic Low-Voltage, Fluorescent, Fan Control















Features



- Preset feature allows user to return to previous light setting when turning lights on
- Integrated linear slide control for easy, precise operation
- All units are available in combined Single-Pole/3-Way versions
- Incandescent and Magnetic Low-Voltage offered in single unit version
- Neutral is not required for installation of device
- Replaces a standard switch and offers dimmer capabilities
- Square law dimming - perceived dimming level is proportional to the slider position
- Power failure memory
- Radio Frequency Interface (RFI) filtering is standard on all models
- Electrostatic discharge protection
- Precise color matching
- Quiet Fan Speed Control version has special circuitry to reduce fan motor noise at low speeds
- Compatible with any decorator wallplate or screwless wallplate



DI06P-W
PJS26W Wallplate

Available Color Options	Load Types	Wiring Types
 Almond	 Incandescent/Halogen	 Single-Pole and 3-Way
 Black	 Fluorescent	
 Brown	 Magnetic Low-Voltage	
 Gray	 Electronic Low-Voltage	 Single-Pole and 3-Way Fan Control
 Ivory	 3-Speed Fan Control	
 Light Almond		
 White		

Finishing touch to your decorator installation

DEVINE dimmers offer the ideal solution with a contemporary design, accurate light level control, combined Single-Pole and 3-Way units, broad color selection and compatibility with popular lamp types.



DI06P-A
PJS26LA Wallplate

DEVINE Slide Dimmer and Fan Control



Wattage	Lamp Type	Descriptions	Cat. No.	Color
600W/VA	Incandescent, Halogen, MLV	Dimmer, Single-Pole & 3-Way with Preset	□ DI06P- __	A, B, BK, GY, LA, V, W
1000W/VA	Incandescent, Halogen, MLV	Dimmer, Single-Pole & 3-Way with Preset	□ DI10P- __	A, B, BK, GY, LA, V, W
600W	ELV	Dimmer, Single-Pole & 3-Way with Preset	□ DE06P- __	A, B, BK, GY, LA, V, W
8A	Fluorescent (Mark 10®, AmbiStar® & Tu-Wire®)	Dimmer, Single-Pole & 3-Way with Preset	□ DF8AP- __	A, B, BK, GY, LA, V, W
8A	Fluorescent (Mark 10®)	Dimmer, Single-Pole & 3-Way with Preset, 277V	□ DF8AP7- __	A, B, BK, GY, LA, V, W
1.5A	Quiet 3-Speed	Fan Speed Control, Single-Pole & 3-Way	□ DFS15P- __	A, B, BK, GY, LA, V, W

To indicate color when ordering, add one of the following suffixes to the Catalog Number: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

Note: All DEVINE dimmers and fan speed controls are rated for 120V/AC unless otherwise noted.

For more information see specification information on page 50.

Derating information shown on page 47.

Accessory Products



9534DS
ASPIRE Dimmer



AIM10-A
ACCELL Dimmer



7501A
Switch



VGF15A
GFCI



PJS26A
Receptacle