



BURNDY Catalog Number YGHA31N
UPC Number 7818102099366
Description 350 HVYDTY CULUG-1/2NEMA
Status Active

Web Use
BURNDY Product Line

Dimensional
Thickness 0.43
B Length (in) 1.18
D - in 1.27
Pad Width (in) 1.62

Product Description

General

Copper Hylug Heavy Duty, Ground,
350 kcmil 12,19,37 Str., 3.20 in L,
Suitable For Direct Burial in Earth
or Concrete

Copper Solid Size (Range)
Copper Stranded (Range)

Conductor(s)

N/A
350 kcmil

Type of Plating
Connector Type
Plated (Yes or No)
Index Number

Physical

Unplated
Terminal
N
20

Rated for Direct Burial
UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards
Documentation

Approvals / Certifications

Y
N
N
Compliant
N
N
UL468A-468B,UL467,IEEE 837

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175