



BURNDY Catalog Number YGHA28NTN
UPC Number 7818102348600
Description 4/0 CUHVYDITYGRD TINPLATE
Status Active

Web Use
BURNDY Product Line

Dimensional
Thickness 0.30
B Length (in) 1.18
D - in 1.27
Pad Width (in) 1.22

General
Product Description Compression Terminals, 4/0
7,12,19, 3.18 in L, Tin Plated,
Suitable For Direct Burial in Earth
or Concrete

Conductor(s)
Copper Solid Size (Range) N/A
Copper Stranded (Range) 4/0 AWG

Physical
Type of Plating Tin - Electro Plated
Connector Type Terminal
Plated (Yes or No) Y
Index Number 17

Approvals / Certifications
Rated for Direct Burial Y
UL Listed N
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B,UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175