







# Code•Master™ Incandescent Factory Sealed Luminaires

## Explosionproof, Dust-Ignitionproof

For use with threaded metal conduit.

**NEC:**

Class I, Division 1, Groups C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 3R, 4X

	Description	Weight kg (lb)	Catalog Number
<b>Fixture Unit Only</b>			
	Not including mounting hood	5.0 (11.02)	CJNC30I
<b>Optional White Polyester Reflector</b>			
	Standard Dome	1.1 (2.43)	KR2-ST
<b>Optional White Polyester Reflector</b>			
	Angled Reflector	1.1 (2.43)	KR2-AN
<b>Optional Aluminum Guard</b>			
		0.2 (0.44)	CJGU-15
<b>Optional Three Way Exit Sign</b>			
		3.4 (7.50)	CJEXRN
<b>Replacement Connection Block</b>			
		0.2 (0.44)	VPT-7

Appleton®

INCANDESCENT/AREA: NEC/CEC EXPLOSIONPROOF