

# Intraground™ N1 and N2 Series Control Station

## Nonmetallic

10 Ampere, 600 Vac Max. for Heavy Duty Use. N1 Series – Neutral Color; N2 Series – Blue Color.


### NEC:

Class I, Division 1 and 2, Groups B\*, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III

### Push Button Accessories and Parts

Description	Catalog Number
-------------	----------------

#### Push Button Securing Rod with Chain – Stainless Steel



For use with Single Guard Only

NBL-SR

#### Mushroom Head Button with Weather Boot for Use with Momentary Contact – Gasketed



Black  
Green  
Red

NMRB-BL  
NMRB-GR  
NMRB-RE

#### Mushroom Head Push Button



For Use with Mushroom Head Push Button – Maintained Contact – Solid-Colored Nonmetallic  
Red

NMRBM-RE



MNPESTPQ

#### Nameplates – Mushroom Head Push Button For Momentary and Maintained

Start	MNPSTQ
Stop	MNPSPQ
Emergency Stop	MNPESTPQ
Blank	MNPBQ

#### Pilot Light, Factory Sealed



Pilot Light



Chamber Only

#### Incandescent

Furnished with 6S6 120 Vac incandescent lamp, jewel and guard. Has 457 mm (18") long, type SFF-2 pigtail leads; +150 °C (+302 °F). Body has 3/4" straight thread (NPSM).

With Red Jewel	SPLSREB
With Green Jewel	SPLSGRB
With Amber Jewel	SPLSAMB
With Blue Jewel	SPLSBLB
With Clear Jewel	SPLSCLB
With Opal Jewel	SPLSOPB

#### LED

Furnished with candelabra base 120 Vac LED, jewel and guard. Has 457 mm (18") long, type SFF-2 pigtail leads; +150 °C (+302 °F). Body has 3/4" straight thread (NPSM).

With Red LED, Clear Jewel	SPLNSREB
With Green LED, Clear Jewel	SPLNSGRB
With Amber LED, Clear Jewel	SPLNSAMB

<b>Chamber Only</b> (Same as above, less jewel, guard and lamp)	SPLSSCB
---	---------

♦ Suitable for Class I, Group B when installed in an enclosure rated for Class I, Group B.