

Auxiliary contact blocks



CA4-10



CAL4-11



CA4-22M



CAT4-11E

5

Description

The auxiliary contact blocks are used for the operation of auxiliary circuits and control circuits for standard industrial environments.

Types of auxiliary contact blocks for front mounting:

- CA4 1 or 4-pole block, with instantaneous N.O., N.C. contacts
- CC4 1-pole block, with N.O. leading contact or N.C. lagging contact
- CAT4 2-pole block, with instantaneous N.O. + N.C. contacts and A1 / A2 coil terminal connection on front face.

Select the 4-pole auxiliary contact blocks CA4-..E, CA4-..M, CA4-..U or CA4-..N type, according to the contactor or contactor relay type for compliance with the standard requirements (see "Terminal marking and positioning").

Types of auxiliary contact blocks for side mounting:

- CAL4 2-pole block, with instantaneous N.O. + N.C. contacts.

For clipping onto the right and/or lefthand side of the contactors.

The auxiliary contact blocks are equipped with screw type connecting terminals delivered open, protected against accidental direct contact and bear the corresponding function marking.

Ordering details (1)

For contactors	Auxiliary contacts	Type	Order code	Pkg qty	Weight (1 pce)
					kg

Front-mounted instantaneous auxiliary contact blocks

AF09 ... AF38 4-pole NF	1 0 - -	CA4-10	1SBN010110R1010	1	0.014
	1 0 - -	CA4-10-T	1SBN010110T1010	10	0.014
	0 1 - -	CA4-01	1SBN010110R1001	1	0.014
	0 1 - -	CA4-01-T	1SBN010110T1001	10	0.014
AF09 ... AF16..-30-10	2 2 - -	CA4-22M	1SBN010140R1122	1	0.055
	3 1 - -	CA4-31M	1SBN010140R1131	1	0.055
	1 3 - -	CA4-13M	1SBN010140R1113	1	0.055
	0 4 - -	CA4-04M	1SBN010140R1104	1	0.055
AF26 ... AF38..-30-00	2 2 - -	CA4-22E	1SBN010140R1022	1	0.055
AF09 ... AF38..-40-00	3 1 - -	CA4-31E	1SBN010140R1031	1	0.055
AF09 ... AF38..-22-00	4 0 - -	CA4-40E	1SBN010140R1040	1	0.055
AF26 ... AF38..-30-00	0 4 - -	CA4-04E	1SBN010140R1004	1	0.055
AF09 ... AF16..-30-01	2 2 - -	CA4-22U	1SBN010140R1322	1	0.055
	3 1 - -	CA4-31U	1SBN010140R1331	1	0.055
	4 0 - -	CA4-40U	1SBN010140R1340	1	0.055
4-pole NF	4 0 - -	CA4-40N	1SBN010140R1240	1	0.055
	3 1 - -	CA4-31N	1SBN010140R1231	1	0.055
	2 2 - -	CA4-22N	1SBN010140R1222	1	0.055
	1 3 - -	CA4-13N	1SBN010140R1213	1	0.055
NF..40E	0 4 - -	CA4-04N	1SBN010140R1204	1	0.055

Front-mounted auxiliary contact blocks with N.O. leading contact and N.C. lagging contact

AF09 ... AF38 4-pole NF	- - 1 0	CC4-10	1SBN010111R1010	1	0.014
	- - 0 1	CC4-01	1SBN010111R1001	1	0.014

Side-mounted instantaneous auxiliary contact blocks

AF09 ... AF38 NF	1 1 - -	CAL4-11	1SBN010120R1011	1	0.040
	1 1 - -	CAL4-11-T	1SBN010120T1011	10	0.040

Front-mounted instantaneous auxiliary contact and A1/A2 coil terminal blocks

AF09 ... AF16..-30-10	1 1 - -	CAT4-11M	1SBN010151R1111	1	0.040
AF26 ... AF38..-30-00	1 1 - -	CAT4-11E	1SBN010151R1011	1	0.040
AF09 ... AF38..-40-00					
AF09 ... AF38..-22-00					
AF09 ... AF16..-30-01	1 1 - -	CAT4-11U	1SBN010151R1311	1	0.040

(1) For each contactor or contactor relay type, refer to "Accessory fitting details" table.

Note: CAT4 not fittable on AF.Z contactors with DC control voltage 12...20 V DC.