

# Circuit Breakers

## Lug Data

*Reference*

1 Load Centers & Circuit Breakers

Circuit Breaker Type	Circuit Breaker Ampere Rating	Cables Per Connector	Connector Wire Range
<b>QP, QPH, HQP, Plug-in</b>	<b>LOAD SIDE</b>		
	10	2	#16 AWG Cu
	15–20	1 1	#14–#8 AWG Cu #12–#8 AWG Al
	25–35	1 1	#14–#6 AWG Cu #14–#6 AWG Al
	40–50	1 1	#8–#6 AWG Cu #8–#4 AWG Al
	55–70	1 1	#8–#4 AWG Cu #8–#2 AWG Al
	80–100	1 1	#4–#1/0 AWG Cu #2–#1/0 AWG Al
	110–125 <sup>®</sup>	1 1	#2–#1/0 AWG Cu #1/0–#2/0 AWG Al
<b>QT</b>	15–35	1 1	#14–#8 AWG Cu #12–#8 AWG Al
	40	1	#8 AWG CU-AL
	40–50	1 1	#8–#6 AWG Cu #8–#4 AWG Al
<b>QPF, QPHF</b>	15–30	1 1	#14–#10 AWG Cu #12–#8 AWG Al
	40–60	1 1	#8–#6 AWG Cu #8–#4 AWG Al
<b>QAF, QAFH</b>	15–20	1 1	#14–#12 AWG Cu #12–#10 AWG Al
<b>QD</b>	15–20	2	#14–#8 AWG Cu Only
	15–20	1	#14–#12 AWG Cu #12–#10 AWG Al
	25–35	1 1	#10–#8 AWG Cu #10–#6 AWG Al
	40–60	1 1	#8–#6 AWG Cu #8–#4 AWG Al
<b>QN, QNH, HQN</b>	150–200	1	#1–300kcmil Cu-Al
<b>EQ8681-Ultimate</b>	100	1	#4–3/0 AWG Cu-Al
<b>EQ8682-Ultimate</b>	125	1	#4–3/0 AWG Cu-Al
<b>EQ8693-Ultimate</b>	150	1	#1–300kcmil Cu-Al
<b>EQ8695-Ultimate</b>	200	1	#1–300kcmil Cu-Al
<b>EQ8696-Ultimate</b>	225	1	#1–300kcmil Cu-Al
<b>QPP, QPPH, HQPP, HQPPH</b>	125	1 1	#1 AWG Cu #2/0 AWG Al
	150	1 1	#1/0 AWG Cu #3/0 AWG Al
	175	1 1	#2/0 AWG Cu #4/0 AWG Al
	200	1 1	#3/0 AWG Cu 250kcmil AWG Al
	225	1 1	#4/0 AWG Cu 300kcmil AWG Al
	<b>EQ9675-EQIII</b>	100	1 1
<b>EQ9677-EQIII</b>	125	1 1	#1 AWG Cu #2/0 AWG Al
<b>EQ9683-EQIII</b>	150	1 1	#1/0 AWG Cu #3/0 AWG Al
<b>EQ9685-EQIII</b>	200	1 1	#3/0 AWG Cu 250kcmil AWG Al
<b>EQ9686-EQIII</b>	225	1 1	#4/0 AWG Cu 300kcmil AWG Al
<b>QPJ</b>	125–200	1	#2–300kcmil Cu-Al