

Photo Not Available



BURNDY Catalog Number CJC34C26  
UPC Number 7818104191822  
Description 300-500 TO 1-2/0 GRDC TP  
Status Active

Web Use  
BURNDY Product Line

|                               |   |
|-------------------------------|---|
|                               | Dimensional   |
| Length (in)                   | 0.88  |
| Height (in)                   | 2.39  |
|                               | General   |
| Product Description           | Cu Compression Ground Tap Connector, 300 - 500 Kcmil (Run), 6 Sol. - 2 Str. (Tap) |
|                               | Conductor(s)  |
| Copper Tap Range              | 7 AWG-2/0 AWG   |
| Copper Stranded Run (Range)   | 300 kcmil-500 kcmil   |
| Rod Size Run (Range)          | N/A   |
| Copper Solid Tap (Range)      | 6 AWG-3/0 AWG   |
| Rebar Run Size (Range)        | N/A   |
| Copper Solid Run Size (Range) | N/A   |
|                               | Physical  |
| Type of Plating               | Unplated  |
| Connector Type                | Tap   |
| Plated (Yes or No)            | N   |
| Product Material              | Copper  |
|                               | Approvals / Certifications  |
| Rated for Direct Burial       | Y   |
| UL Listed                     | Y   |
| CSA Certified                 | Y   |
| ROHS Compatible               | Compliant   |
| UL Recognized                 | N   |
| CULUS                         | N   |
| Documentation                 |   |

For further technical assistance, please contact us

BURNDY LLC - USA  
47 East Industrial Park Drive  
Manchester NH 03109

BURNDY Technical Services  
47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175