

# Electronics Long-Nose Pliers

## Curved Long Needle-Nose Pliers – Extra-Slim

Additional Features:

- 60° bent nose for maximum work visibility in confined areas.
- Easily bends and forms fine wire.
- Polished inside jaws and radiused jaw edges prevent nicking wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D338-5 1/2C

| Cat. No.    | Overall Length  | Jaw Length     | Jaw Width    | Jaw Thickness | Point Thickness | Handle Finish  | Handle Color | Weight (lbs.) |
|-------------|-----------------|----------------|--------------|---------------|-----------------|----------------|--------------|---------------|
| D338-5 1/2C | 5-1/2" (140 mm) | 1-1/2" (38 mm) | 1/2" (13 mm) | 5/16" (8 mm)  | 1/16" (1.6 mm)  | plastic-dipped | dark blue    | .14           |

## Curved Long-Nose Pliers

Additional Features:

- 70° bent nose for maximum work visibility in confined areas.
- Knurled jaws for sure wrapping and looping.
- Curved handles provide greater tool control.



D302-6

| Cat. No. | Overall Length  | Jaw Length     | Jaw Width      | Jaw Thickness | Point Thickness | Handle Finish  | Handle Color | Weight (lbs.) |
|----------|-----------------|----------------|----------------|---------------|-----------------|----------------|--------------|---------------|
| D302-6   | 6-3/8" (162 mm) | 1-1/2" (38 mm) | 11/16" (18 mm) | 3/8" (10 mm)  | 3/32" (2 mm)    | plastic-dipped | yellow       | .30           |

## Midget Curved Chain-Nose Pliers

Additional Features:

- 60° bent nose for maximum work visibility in confined areas.
- Easily bends and forms fine wire.
- Polished inside jaws and radiused jaw edges prevent nicking wire.
- Spring-loaded for self-opening action.
- Curved handles provide greater tool control.



D320-4 1/2C

| Cat. No.    | Overall Length  | Jaw Length | Jaw Width      | Jaw Thickness | Point Thickness | Handle Finish  | Handle Color | Weight (lbs.) |
|-------------|-----------------|------------|----------------|---------------|-----------------|----------------|--------------|---------------|
| D320-4 1/2C | 4-3/4" (121 mm) | 1" (25 mm) | 13/32" (10 mm) | 1/4" (6 mm)   | 1/16" (1.6 mm)  | plastic-dipped | royal blue   | .13           |

## Special Use Long-Nose Pliers

### Conduit Locknut and Reaming Pliers

Additional Features:

- Tightens 1/2" and 3/4" EMT or 1/2" rigid locknuts.
- Fits liquid tight fittings and caps.
- Reams and smooths both inside and outside of conduit.
- Knurled jaws at nose tip pull wire or fish tape.
- Machined nose fits snugly into locknut wings.



D333-8



| Cat. No. | Overall Length  | Jaw Length     | Jaw Width      | Jaw Thickness | Point Thickness | Handle Finish  | Handle Color | Weight (lbs.) |
|----------|-----------------|----------------|----------------|---------------|-----------------|----------------|--------------|---------------|
| D333-8   | 7-3/4" (197 mm) | 1-5/8" (41 mm) | 15/16" (24 mm) | 1/2" (13 mm)  | 3/16" (4.8 mm)  | plastic-dipped | yellow       | .55           |

### Needle-Nose Pliers – Fatigue Reducing

Additional Features:

- Handles minimize bending of wrist to reduce strain and fatigue.
- Knurled jaws for sure wrapping and looping.
- Spring-loaded for self-opening action.



D366-6C

| Cat. No. | Overall Length | Jaw Length       | Jaw Width      | Jaw Thickness | Point Thickness | Handle Finish | Handle Color | Weight (lbs.) |
|----------|----------------|------------------|----------------|---------------|-----------------|---------------|--------------|---------------|
| D366-6C  | 8" (203 mm)    | 1-15/16" (49 mm) | 11/16" (18 mm) | 3/8" (10 mm)  | 1/16" (1.6 mm)  | foam plastic  | red          | .38           |

All dimensions are in inches and (millimeters).

**WARNING:** Always wear approved eye protection.

**WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



# Diagonal-Cutting Electronics Pliers

## Midget Diagonal-Cutting Pliers – Nickel Ribbon Wire Cutters

Additional Features:

- Designed to cut nickel ribbon wire.
- Nose tip is only 1/32" (0.8 mm) for precise work in confined areas.
- Tip cutting knife is 3/16" (5 mm) long for precise cutting.
- Spring-loaded action for self-opening.



D230-4C

| Cat. No. | Overall Length  | Jaw Length   | Jaw Width     | Jaw Thickness | Cutting Knives | Handle Finish  | Handle Color | Weight (lbs.) |
|----------|-----------------|--------------|---------------|---------------|----------------|----------------|--------------|---------------|
| D230-4C  | 4-1/4" (108 mm) | 1/2" (13 mm) | 7/16" (11 mm) | 1/4" (6 mm)   | semi-flush     | plastic-dipped | royal blue   | .12           |

## Lightweight Flush Cutter

Additional Features:

- Shears wire up to 18 AWG producing a flat, flush cut.
- Shear cutting greatly reduces cutting effort and minimizes fly-off.
- Cushioned grips and steel return spring for increased comfort during repetitive cutting.
- Ultra slim profile increases access in confined areas.
- Heat treated for increased durability.



D275-5

| Cat. No. | Overall Length | Cutting Knives | Handle Finish | Handle Color | Weight (lbs.) |
|----------|----------------|----------------|---------------|--------------|---------------|
| D275-5   | 5" (127 mm)    | flush          | plastic       | red          | .11           |

## Long-Nose Pliers

Features:

**Custom, US-made tool steel.**

**Hot-riveted joint** ensures smooth action and no handle wobble.

**Plastic-dipped handles<sup>†</sup>** for comfort and ease of identification.

**Slim head design** for working in confined areas.

<sup>†</sup>Journeyman pliers available. State-of-the-art, dual-material handles, which provide a better grip without sacrificing tool strength or durability.

All dimensions are in inches and (millimeters).

**▲WARNING:** Always wear approved eye protection.

**▲WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.