



BURNDY Catalog Number YAV2/0T12B
UPC Number 7818104256199
Description CANLUG-2/0 FLEX-1/2-BELL
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.20
Barrell Style	Belled
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.13
B Length (in)	0.74
Pad Width (in)	0.91
General	
Number of Holes	1
Product Description	Pure Electrolytic Seamless Cu Tube Compression Terminal, 1 Hole W/InspWindow, 2/0 AWG Flex, 1/2" Stud, Belled End
Conductor(s)	
Aircraft Cable Size (Range)	N/A
Flex (Class H) Size - Range	2/0 AWG
Flex (Class I) Size - Range	2/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	N/A
Flex (Class G) Size - Range	2/0 AWG
Flex (Class M) Size - Range	2/0 AWG
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Black
Plated (Yes or No)	Y
Product Material	Copper
Approvals / Certifications	
UL Listed	N
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175