

Photo Not Available



BURNDY Catalog Number CJC29C29
 UPC Number 7818104191755
 Description 3/0-250 TO 3/0-250 GRD C
 Status Active

Web Use
 BURNDY Product Line

| | |
|-------------------------------|--|
| | Dimensional |
| Length (in) | 0.83 |
| Height (in) | 2.06 |
| | General |
| Product Description | ETP Cu Comp Ground Tap Connector, 3/0 Str-250 kcmil(Run), 3/0 Str-250 kcmil(Tap) |
| | Conductor(s) |
| Copper Tap Range | 3/0 AWG-250 kcmil |
| Copper Stranded Run (Range) | 3/0 AWG-250 kcmil |
| Rod Size Run (Range) | N/A |
| Copper Solid Tap (Range) | 3/0 AWG-4/0 AWG |
| Rebar Run Size (Range) | N/A |
| Copper Solid Run Size (Range) | 3/0 AWG-4/0 AWG |
| | Physical |
| Type of Plating | Unplated |
| Connector Type | Tap |
| Plated (Yes or No) | N |
| Index Number | CSA28CU |
| Product Material | Copper |
| | Approvals / Certifications |
| Rated for Direct Burial | Y |
| UL Listed | Y |
| CSA Certified | Y |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| CULUS | N |
| Documentation | |

For further technical assistance, please contact us

BURNDY LLC - USA
 47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services
 47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175