

Boxes and Covers

. . .

Device Boxes – Available Models

Technical Specifications

		Gangable									Non-Gangable											
	Depth	1 1/2	2	2	2	2 1/4					2 1/2	2 1/2	2 1/2	3	3	3		2 1/2				2 1/2
	Cu. in.	8.0	10.0	10.0	12.0	10.0	12.5	12.5	14.5	12.5	12.5	16.0	18.0	15.0	18.0	18.0	11.0	12.5	14.5	15.0	18.5	25.0
	Series # BC/CI	1100	1102		3102		525				4304			1004	1018		777		2304			4204
	Basic Model		\checkmark	\checkmark				\checkmark						\checkmark								
	В							✓														
its It	К							\checkmark														
in l	KSSX											\checkmark										\checkmark
Conduit Knockouts	KSS1X-1											\checkmark										
ŬĔ	LE							✓														
<u> </u>	SB		\checkmark					\checkmark														
	SSX				✓							✓										
	L	\checkmark	✓	√		✓	✓	✓		✓				√								
	LB							✓						√								
	LD					✓																
S	LH	\checkmark										\checkmark	\checkmark	\checkmark		\checkmark					\checkmark	
Nonmetallic Sheathed Cable Clamps (Loomex, NMD90)	LHT							✓						· ·								
ar	LHTQ								\checkmark			\checkmark			\checkmark				\checkmark			
U O	LLE	\checkmark																\checkmark		\checkmark		
ble 0)	LHTQ-2/LLE-2	-																\checkmark		-		
D9 D9	LHTQ-3/LLE-3																	\checkmark				
Σg	LHTQ-4/LLE-4																	\checkmark				
, Ne	LMS							~											✓			
eat	LN							•										✓	•			
Sh	LRB																\checkmark	-				
<u>°</u>	LRE	\checkmark															-					
	LRW							✓														
Jet	LSSX							•			✓	✓				✓		✓				✓
E	LSS2X										-	-				-		\checkmark				
Ž	LSS3X																	✓				
	LSSX-1															✓		•				
	LSS1X-1															•		\checkmark				
	LSS2X-1																	\checkmark				
	LX																	\checkmark			\checkmark	
Armoured Cable Clamps (BX, AC90)	LA							✓		\checkmark												
	LBA							· √														
	LHA							· √				\checkmark	\checkmark	\checkmark							√	
	LLEA																	✓				
	LLEA-2																	· •				
	LMSA							✓														
	LSBA							· √														
ou	LSSAX				✓						 ✓ 	\checkmark						\checkmark		✓		✓
Arr Iar	LSSAA LSSA-2X										-							• √				
O O	LSSA-2X LSSA-3X																	▼ √				
	LSSA-3X LSSAX-1															\checkmark		-				✓
												\checkmark				•						v
	LSSA1X-1											V										



Boxes and Covers



Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps







BC2304-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



BC2304-LHTQ-2

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs One screw mounting.

BC2304-LHTQ-3

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs

BC2304-LHTQ-4

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.

BC3104-LHTQ Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.

One screw mounting

Oct. No.	Dimensions	Volume	Gangable		Pryouts			
Cat. No.	H x W x D (in.)	(Cu. in.)	Yes or No	One screw mounting	Pos. tabs	Prov. for external nailing	ends	
BC1018-LHTQ	3 x 2 x 3	18.0	yes	yes	yes	yes	4	
BC1304-LHTQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4	
BC1304-LHATQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4	
BC2004-LHTQ	3-3/4 x 2-3/16 x 2-3/4	20.5	no	yes	yes	yes	4	
BC2304-LHTQ	3 x 2 x 2-1/2	14.5	no	yes	yes	yes	4	
BC2304-LHTQ-2	3 x 3-3/4 x 2-1/2	27.0	no	yes	yes	yes	8	
BC2304-LHTQ-3	3 x 5-1/2 x 2-1/2	39.5	no	no	yes	yes	12	
BC2304-LHTQ-4	3 x 7-3/8 x 2-1/2	52.0	no	no	yes	yes	16	
BC3104-LHTQ	3 x 2 x 2-1/2	16.0	yes	yes	yes	yes	4	






lberville°

Boxes and Covers

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps



Features **Pryouts** Width Volume Cat. No. (in.) (Cu. in.) Ears Bracket ends 2-1/2 in. Deep — Non-Gangable — 3 in. High BC2104-LLE 2 12.5 P. Tabs 4 -BC2104-LLE-2 3-3/4 P. Tabs 8 25.0 BC2104-LLE-3 5-1/2 37.5 P. Tabs 12 BC2104-LLE-4 7-3/8 50.0 -P. Tabs 16 BC2104-LN 2 12.5 -P. Tabs/Nails 4 BC2104-LX 2 12.5 P. Tabs 4 BC2304-LHTQ 2 14.5 P. Tabs 4 -BC2304-LHTQ-2 3-3/4 27.0 P. Tabs 8 -BC2304-LHTQ-3 P. Tabs 12 5-1/2 39.5 -BC2304-LHTQ-4 7-3/8 52.0 P. Tabs 16 BC2104-LRB 2 12.5 4 --BC2104-LRB-2 3-3/4 25.0 8 --

