



On Line Catalog

Photo Not Available



BURNDY Catalog Number CJC34C29
UPC Number 7818104191999
Description 300-500 TO 3/0-250 GRD C
Status Active

Web Use
BURNDY Product Line

	Dimensional
Length (in)	0.88
Height (in)	2.65
	General
Product Description	ETP Cu Comp Ground Tap Connector, 300 - 500 kcmil(Run), 3/0 Str-250 kcmil(Tap)
	Conductor(s)
Copper Tap Range	3/0 AWG-250 kcmil
Copper Stranded Run (Range)	300 kcmil-500 kcmil
Rod Size Run (Range)	N/A
Copper Solid Tap (Range)	N/A
Rebar Run Size (Range)	N/A
Copper Solid Run Size (Range)	N/A
	Physical
Type of Plating	Unplated
Connector Type	Tap
Plated (Yes or No)	N
Product Material	Copper
	Approvals / Certifications
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services
47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175