Commercial Grade Fittings

Nonmetallic Sheathed Cable

Connectors

Cat. No.	Trade Size (in.)	Clamping Range (in.)		Suggested Application
		Min.	Max.	NMD90 (loomex)
One Screw Fittings (Aluminum)				
CI2166	1/2	0.50	0.90	8/3-6/3
CI2167	3/4	0.71	1.10	6/3-4/3
Duplex Fittings (Zinc Alloy)				
One Screw Cl2175	3/8	0.15	0.65	14/2-10/2; 14/3-10/3
Nonmetallic Fittings				
CI3360		0.30	0.60	14/2-10/2; 14/3-10/3 2 cables: 14/2-12/2
C14004	1/2	0.21	0.42	14/2-10/2; 14/3-10/3 2 cables: 14/2-12/2
W100LX-D		0.21	0.42	14/2-10/2; 14/3-10/3 2 cables: 14/2-12/2
One Screw Fittings (Steel)				
C14040	3/8	0.19	0.57	14/2-10/2; 14/3-10/3 2 cables: 14/2
CI9049		0.13	0.37	14/2-10/2; 14/3-12/3

CI2166 / CI2167



Zinc Die Cast Locknut

CI4004 / W100LX-D





CI2175

Zinc Die Cast Locknut

CI4040



CI3360



CI9049



All NMD90 fittings are also suitable for NMWU90 of equivalent diameters, in dry locations NOTE: 3/8 in. trade size connectors require a 1/2 in. knockout

Technical improvements are constantly taking place in the electrical industry. Cable manufacturers are changing their products from time to time. Accordingly, it is strongly suggested that you verify the cable size with the cable manufacturer prior to selecting a fitting.





Ð