



EI400WC



White



Ivory



Light Almond



Ratings	
Operating Voltage	120-277 VAC 12-28 VDC
Resistive	20 A
Incandescent	15 A, 120 VAC 6 A, 208-277 VAC
Inductive Ballast (Fluorescent)	16 A, 120-277 VAC
Motor	1 HP, 120 VAC 2 HP, 240 VAC
DC Loads	4 A, 12 VDC 2 A, 28 VDC
Operating Temperature	32° F to 122° F (0° C to 50° C)
Dimensions H x W x D	4 1/8" x 1 3/4" x 1 3/16" (104.8 mm x 44.5 mm x 30.2 mm)
Warranty	5-year limited

Note: Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

## Programmable Electronic Countdown Timer

### EI400 Series

Offering a programmable countdown time between one-second and 24-hours, this versatile timer can handle any application, regardless of load type. No neutral connection is required.

#### Features

- Programmable countdown time interval from one-second to 24-hours
- Settings stored in non-volatile memory
- Optional audible and/or visual warning of impending load switch OFF
- Lockable settings help avoid unintended changes
- Single pole or 3-way switch compatible installation
- Incandescent/fluorescent/CFL/LED compatible
- Isolated switch allows timer to be used with any load type including AC and DC loads
- Replaceable CR2 lithium battery provides up to three years of operation
- No neutral wire connection enables easy retrofitting and quicker installation

White	Ivory	Light Almond
EI400WC	EI400C	EI400LAC

## Countdown Timer Applications

- Bathroom fans • Spas • Hot tubs • Storage closets • Garage lights

