# deQUORUM™ RECESSED WORK SURFACE PORTALS



deQuorum™ Recessed Work Surface Portals provide flexibility in décor, communication and A/V connectivity options, and installation to meet specific functional and aesthetic needs.

#### **CODE REFERENCE**

cULus Listed Relocatable Power Tap: File E66421 Guide XBYS cULus Listed Multioutlet Assembly: File E15191 Guide PVGT Listed to US and Canadian Safety Standards Meets Article 380 of NEC.


#### deQuorum Recessed Work Surface Portals Part Number Configurator

	_				
deQuorum Series:	Cover Style:	Cover Color:	Communication:	Top Style:	
KC = Cord Ended KF = Field Installed	Flush = 1 Contoured = 4	Black = 0 Gray = 5	Ortronics = RT Wiremold = CM Open System	Recessed = 2 Blank = 8	


NOTE: Part Number Configurator can be used both to identify stock product configurations and also to request custom configurations from the factory. Consult the factory for more information.

#### deQuorum Recessed Work Surface Portals Cover Options

**Flush Covers -** Available finishes: Black or Gray. Shown with flange.



Decorative Recess for Table Laminate Insert **Contoured Covers -** Available finishes: Black or Gray. Shown with flange.



Decorative Recess for Table Laminate Insert

#### **COLOR OPTIONS**





deQuorum Work Surface Portal Covers are available in Black or Gray

For information regarding communication inserts, go to: www.legrand.us/wiremold

## deQUORUM™ RECESSED WORK SURFACE PORTALS

Ordering Information

deQuorum Recessed Work Surface Portals - In-Stock Configurations Ordering Information

#### **KC10CM2**

Cord-ended with black, flush cover with decorative recess. Unit comes with two 20A gasketed prewired receptacles with a 12' [3.65m] 14/3 SJT black cord. Includes adapter for Wiremold CM Series Open System communications outlets. Communication modules sold separately.

#### KF10CM8


Field-wired with black, flush cover. Unit comes with two 20A gasketed prewired receptacles with a 3/8" [9.5mm] diameter 6' [1.83m] flexible whip. Includes adapter for Wiremold CM Series Open System communications outlets. Communication modules sold separately.

### KC10RT8

Cord-ended with black, flush cover. Unit comes with two 20A gasketed prewired receptacles with a 12' [3.65m] 14/3 SJT black cord. Includes adapter for Ortronics® Series II and TracJack inserts. Communication modules sold separately.

## **KC15RT8**


Cord-ended with gray, flush cover. Unit comes with two 20A gasketed prewired receptacles with a 12' [3.65m] 14/3 SJT black cord. Includes adapter for Ortronics® Series II and TracJack inserts. Communication modules sold separately.



### KF15RT2

Field-wired with gray, flush cover with decorative recess. Unit comes with two 20A gasketed prewired receptacles with a 3/8" [9.5mm] diameter 6' [1.83m] flexible whip. Includes adapter for Ortronics® Series II and TracJack inserts. Communication modules sold separately.

#### Field-Wired Unit





Above unit shown with KA700, 20A Gasketed Receptacle Plate and KA305, Legrand AVIP Adapter Plate installed.