

Panelboards

Type P2 Panelboard Kits and Accessories

Selection

Standard Enclosures

Box Height - Inches (mm)	Catalogue Number			
	Type 1 Standard			Type 3R/12 ^②
	Box	Surface Trim	Flush Trim ^①	
26 (660)	B26	S26B	F26B	WP26
32 (813)	B32	S32B	F32B	WP32
38 (965)	B38	S38B	F38B	WP38
44 (1118)	B44	S44B	F44B	WP44
50 (1270)	B50	S50B	F50B	WP50
56 (1422)	B56	S56B	F56B	WP56
62 (1575)	B62	S62B	F62B	WP62
68 (1727)	B68	S68B	F68B	WP68
74 (1880)	B74	S74B	F74B	WP74

Options For Type 1 Trims

Hinged trim – Replace "B" suffix with "H"

Door-in-door – Replace "B" suffix with "D"

Screw to box – Replace "B" suffix with "C"

Trim with padlock – Add "-PL" suffix

Metal card holder – Add "M" suffix on all trims

Option For 24" Wide Enclosures

24" wide with equal gutter on both sides - Add "24" as prefix

6

PANELBOARDS

^① Flush trim extend 3/4" on each side of the base box.

^② Hinged door included in type 3R/12 enclosures.