

Project Name

Location

Prepared By



## SATCO S11401

9A19/LED/E26/5K/120V/10PK

Notes

[www] 11-09-2020 01:16:22

### General

Status	Active
Watts	9
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

### Physical

MOL	4.38
MOD	2.38

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp