





# Ty-Rap®



**NOTES:**

1. MATERIAL: AS NOTED
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. SMNY-000 ACCEPTS CABLE TIES TO 18 LBS  
 SMNY-001 ACCEPTS CABLE TIES TO 50 LBS  
 SMNY-002 ACCEPTS CABLE TIES TO 120 LBS

CATALOG NUMBER	MATERIAL	COLOR	A	B	C	D SLOT WIDTH	F SLOT HEIGHT	G SCREW SIZE
SMNY-000-9-**-	NYLON 6,6	NATURAL	.570 [14,47]	.340 [8,63]	.270 [6,85]	.120 [3,04]	.070 [1,77]	.112 [M3 x 0,5]
SMNY-001-9-**-			.600 [15,24]	.385 [9,77]	.280 [7,11]	.200 [5,08]	.060 [1,52]	.138-.164 [M4 x 0,7- M4,5 x 0,75]
SMNY-002-9-**-			.875 [22,22]	.625 [15,87]	.390 [9,90]	.325 [8,25]	.090 [2,28]	.164-.190 [M4,5 x 0,7- M5 x 0,8]
SMNY-001-0-**-	HEAT STABILIZED NYLON 6,6	BLACK	.600 [15,24]	.385 [9,77]	.280 [7,11]	.200 [5,08]	.060 [1,52]	.138-.164 [M4 x 0,7- M4,5 x 0,75]
SMNY-002-0-**-			.875 [22,22]	.385 [9,77]	.280 [7,11]	.200 [5,08]	.060 [1,52]	.164-.190 [M4,5 x 0,7- M5 x 0,8]

\*\* = PACKAGING- C = STD PKG (100) D = BULK PKG (500)

**GENERAL NOTES**

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.

**REVISIONS**

\*\* SEE ERN ( \*\*\*\* ) FOR APPROVAL SIGNATURES & RELEASE DATE.  
 PROJECT NO: \*\*\*\*

**Thomas & Betts**  
 www.tnb.com

DESCRIPTION:

**SADDLE SUPPORT BASE**

ORIGINAL PROJECT NO / ( ERN NO )

**FM401183 / ( 2007645 )**

SHEET NO:

**1 OF 1**

REV. NO:

**\*\***

DRAWING NO:

**WSD-000327**