



KS25

by Burndy
Catalog ID: KS25

Prop 65 Notice

Copper Split Bolt, Cu: 4 AWG-1/0 AWG (Str) (Run & Tap).

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Installation Torque: 385 IN-LB, Length: 1.77 IN, Cross Flats: 0.94 IN, Width: 0.73 IN

Product Details

General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Installation Torque Recommended in-lb	385 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810013106
UPC 12 Digit	7818100131066

Dimensions

Dimension - B Length fraction	83/100 in
Dimension - B Length inch	.83 in
Dimension - Cross Flats inch	0.94 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.77
Dimension - Width fraction	73/100 in
Dimension - Width inch	0.73 in
Dimension - Width mm	19 mm
Width	0.73 in

Conductor Related

Conductor - Copper Solid Run	2/0 AWG
Conductor - Copper Solid Run Range	4 AWG-1/0
Conductor - Copper Solid Tap	2/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-1/0
Conductor - Copper Str Run	4 AWG;3 AWG;2 AWG;1 AWG;1/0

Conductor - Copper Str Run Range	4 STR - 1/0 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Tap Range	4 STR - 1/0 STR
Conductor - CopperWeld Solid Run	2/0
Conductor - CopperWeld Solid Run Range	2/0
Conductor - CopperWeld Solid Tap	2/0
Conductor - CopperWeld Solid Tap Range	2/0
Conductor - CopperWeld Str Run	4 D AWG;4 N AWG;4 P AWG;3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG
Conductor - CopperWeld Str Run Range	4 D AWG-2 A AWG
Conductor - CopperWeld Str Tap	5 D AWG;5 P AWG;4 A AWG;4 D AWG;4 N AWG;4 P AWG;3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG
Conductor - CopperWeld Str Tap Range	5 D AWG-2 A AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)