

## Eaton XB IEC terminal block

**XBUT6**

**UPC:**782116904945

**Dimensions:**

- **Height:** .25 IN
- **Length:** 1.75 IN
- **Width:** .25 IN

**Weight:**.01 LB

**Warranties:**

- 1 year

**Specifications:**

- **Type:** IEC-XB Series
- **Amperage Rating:** 527 (IEC), 40A (EN), 50A (EN), 50A (UL)
- **Voltage Rating:** IEC 800V, EN 700V, UL 600V
- **Maximum Wire Size:** 8 AWG/6 mm<sup>2</sup>
- **Wire Size:** #24-8 AWG
- **Color:** Gray

**Supporting documents:**

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XBUT6 3D Inventor](#)
- [XBUT6 AutoCAD 2D Footprint \(mm\)](#)
- [XBUT6 AutoCAD 2D Footprint](#)
- [XBUT6 2D Drawing Xchange](#)
- [XBUT6 3D Model Xchange](#)
- [XBUT6 2D PDF](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT6](#)

**Certifications:**

- UL Listed
- CSA Certified



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.