

# BA10EF10

by Burndy  
Catalog ID: BA10EF10

Prop 65 Notice

Copper Fork Terminal, 12 - 10 AWG, 600 V, #8 - #10 Stud, Polyvinylchloride Insulation, Tin Plated.

Features: Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, 600 V Maximum, 105 DEG C Maximum, Installation Tool: MR15, M8ND Tool With N10ET-23 Die, Package: Bulk, Insulation Diameter (maximum): 0.26 IN, Color Code: Yellow, Wire Strip Length: 19/64 IN, Temperature Rating: 105 DEG C Maximum, Wire Insulation Grip: No, Finish: Electro-Tin Plated



## Product Details

### General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Connector Type	Terminal - Fork
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUK
Trade Name	VINYLUK™
Type	BA-EF
UPC	781810026533
UPC 12 Digit	7818100265333

### Dimensions

Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	1.07 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	500
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)