

Project Name

Location

Prepared By



Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	6
Incandescent Equivalent	65
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	500
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	11000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60 Hz
CBCP	593
Spot Type	FL - Flood
Dimming Type	Triac
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	3.1
MOD	2.5
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

