

Project Name

Location

Prepared By



Notes

[www] 03-22-2021 04:50:55

General

| | |
|-------------------------|----------------|
| Status | Active |
| Watts | 8.9 |
| Incandescent Equivalent | 75 |
| Volts | 120V |
| Shape | PAR30SN |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 3000 |
| Temperature | Warm White |
| CRI | 80 |
| Lumens | 700 |
| Beam Spread | 40 |
| Dimmable | Yes - Dimmable |
| Hours Rated | 11000 |
| Lamp Type | PAR |
| Technology | LED |

Electrical

| | |
|-----------------------|--|
| Operating Frequency | 60 Hz |
| CBCP | 1315 |
| Spot Type | FL - Flood |
| Dimming Type | Triac |
| Power Factor | 0.7 |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

Physical

| | |
|---------------|-------------|
| MOL | 3.34 |
| MOD | 3.75 |
| Lensed | Lensed Lamp |
| Lens Finish | Clear |
| Lens Material | Plastic |
| Housing Color | White |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|-------------------|---------------------------|
| Safety Listing | cULus |
| Location Rating | Wet |
| Energy Star | No |
| California Status | Non-Compliant |
| Nevada Status | Lawful for sale in Nevada |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |

