

Project Name

Location

Prepared By



Notes

[www] 03-15-2021 00:27:51

General

Status	Active
Watts	8.9
Incandescent Equivalent	75
Volts	120V
Shape	PAR30LN
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	700
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	11000
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60 Hz
CBCP	1315
Spot Type	FL - Flood
Dimming Type	Triac
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.41
MOD	3.75
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

