

Project Name

Location

Prepared By



Notes

[www] 03-15-2021 00:27:51

### General

Status	Active
Watts	13
Incandescent Equivalent	90
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000
Temperature	Warm White
CRI	80
Lumens	1000
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	11000
Lamp Type	PAR
Technology	LED

### Electrical

Operating Frequency	60 Hz
CBCP	1533
Spot Type	FL - Flood
Dimming Type	Triac
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	5.13
MOD	4.75
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

